

KERN MGC 100K-1S05

The classic robust scale to measure body weight quickly

KERN[®]



Construction

Casing material:	Steel lacquered
Dimensions of weighing plate (WxDxH):	265 x 265 x 70 mm
Material weighing plate:	Plastic
Overall dimensions mounted (WxDxH):	285 x 425 x 85 mm
Weighing surface (WxD):	265 x 265 mm

Piktogramme

STANDARD



Measuring system

Adjustment options:	Calibration not possible
Linearity:	2 kg
Readability [d]:	1 kg
Repeatability:	1 kg
Resolution:	150
Stabilisation time under laboratory conditions:	1,500 s
Warm up time:	10 min
Weighing capacity [Max]:	150 kg
Weighing units:	kg

Display

Display digit height (large):	8 mm
-------------------------------	------

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	5 %

Category

Brand:	KERN
Product Group:	Personal floor scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	470 x 315 x 565 mm
Gross weight:	17,500 kg
Net weight:	15,500 kg
Shipping method:	Parcel service