

KERN MWB300K-1



Enormously compact drive-through scale with castors and handles for maximum mobility and space-saving storage



Category

Brand:	KERN
Category:	Balances
Product Group:	Wheelchair platform scale

Packaging & shipping

Delivery:	48 h
Dimensions packaging (WxDxH):	1200 x 1040 x 230 mm
Gross weight:	78 kg
Net weight:	58,900 kg
Shipping method:	Freight forwarder

Construction

Cable length of display device:	3 m
Casing material:	Steel lacquered
Dimensions of display device (WxDxH):	200 x 130 x 60 mm
Dimensions of weighing plate (WxDxH):	1000 x 1000 x 40 mm
Level indicator:	yes
Material weighing plate:	Steel lacquered
Overall dimensions mounted (WxDxH):	1066 x 1000 x 80 mm
Wall mount:	yes
Weighing surface (WxD):	800 x 800 mm

Piktogramme

STANDARD



Measuring system

Adjustment options:	External calibration
Linearity:	100 g
Readability [d]:	100 g
Recommended adjusting weight:	300 kg (M1)
Repeatability:	100 g
Resolution:	3000
Tare range:	-299,900 kg
Warm up time:	10 min
Weighing capacity [Max]:	300 kg
Weighing system:	Strain gauge
Weighing units:	kg

Display

Display digit height (large):	2,500 cm
Display digit height (small):	2,500 cm

Functions

BMI function:	yes
Data hold function:	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	5 %

Power supply

Battery:	6x1.5 V AA
Operating time:	40 h

Services (optional)

Adjustment at the location of installation: 961-249

DAkkS Certificate:	963-129
--------------------	---------