

# KERN PBS620-3M

Multifunctional laboratory balance with single-cell weighing system and EC type approval [M]



## Functions

Capacity display:	yes
Counting function:	yes
Density determination function:	yes
Dispensing function:	yes
Peak function:	yes
Percentage determination:	yes
PRE-TARE function:	yes
Standby function:	yes
Suspended weighing:	Hook
Vibration-free weighing (Animal weighing program):	yes
Weighing with tolerance range:	yes

## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	30 °C
Minimum ambient temperature:	10 °C

## Power supply

Input voltage:	220 V - 240 V AC 50 Hz
Mains adapter:	Mains adapter external
Mains adapter/adapter included:	EURO CH UK US

## Services (optional)

DAkkS Certificate:	963-103
--------------------	---------

## Category

Brand:	KERN
Category:	Balances
Product Group:	Precision balance

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	372 x 585 x 270 mm
Gross weight:	4,140 kg
Net weight:	3,100 kg
Shipping method:	Parcel service

## Construction

Casing material:	Cast aluminium alloys
Dimensions draft shield (WxDxH):	202 x 228 x 103 mm
Dimensions housing (WxDxH):	209 x 322 x 78 mm
Dimensions of weighing plate (WxDxH):	108 x 105 x 5 mm

## Measuring system

Adjustment options:	External calibration
Linearity:	2 mg
Minimum weight (USP):	2 g
Readability [d]:	1 mg
Recommended adjusting weight:	600 g (E2)
Repeatability:	1 mg
Resolution:	620000
Stabilisation time under laboratory conditions:	2,500 s
Warm up time:	4 h
Weighing capacity [Max]:	620 g
Weighing units:	g kg

## Display

Display digit height (large):	1,400 cm
-------------------------------	----------

## Counting

Counting resolution:	620000
Minimum piece weight at piece counting (Laboratory):	1 mg
Minimum piece weight at piece counting (Normal):	10 mg

# KERN PBS620-3M



Multifunctional laboratory balance with single-cell weighing system and EC type approval [M]

Level indicator:	yes
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Weighing space (WxDxH):	180 x 193 x 87 mm
Weighing surface (WxD):	108 x 105 mm

## Piktogramme

### STANDARD



### OPTION



### FACTORY

