

KERN UFN600K200IPM



Pallet scale with stainless steel load support (IP67) and stainless steel display device (IP65), with EC type approval [M]



Weighing with tolerance range: yes

Environmental conditions

Maximum humidity:	95 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	10 %

Power supply

Charging time:	10 h
Input voltage:	110 V - 230 V AC
Mains adapter:	Mains adapter external
Mains adapter/adapter included:	EURO CH UK US
Operating time (Backlight off):	35 h
Operating time (Backlight on):	20 h

Services (optional)

Adjustment at the location of installation: 961-250

DAkkS Certificate:	963-130
Verification:	965-230

Category

Brand:	KERN
Category:	Balances

Packaging & shipping

Delivery:	48 h
Dimensions packaging (WxDxH):	1410 x 910 x 210 mm
Gross weight:	85 kg
Net weight:	50 kg
Shipping method:	Freight forwarder
UN number:	2800

Construction

Cable length:	5 m
Cable length of display device:	5 m
Dimensions of display device (WxDxH):	266 x 165 x 96 mm
Dimensions of weighing plate (WxDxH):	1360 x 840 x 90 mm
Level indicator:	yes
Revolving screw feet:	yes
Wall mount:	yes
Weighing surface (WxD):	1190 x 840 mm

Measuring system

Adjustment options:	External calibration
Linearity:	200 g
Load cell connection:	4-wire
Readability [d]:	200 g
Recommended adjusting weight:	600 kg (M1)
Repeatability:	200 g
Resolution:	3000
Stabilisation time under laboratory conditions:	3 s
Tare range:	-600 kg
Warm up time:	10 min
Weighing capacity [Max]:	600 kg
Weighing system:	Strain gauge
Weighing units:	kg

Display

Display digit height (large):	5,200 cm
-------------------------------	----------

Technical data about verification

Minimum load [Min]:	4 kg
Periodic Verification for Italy:	969-112
Verification approval conforming to 2014/31/EU:	yes
Verification by KERN possible:	yes
Verification class:	III
Verification value [e]:	200 g

Functions

Counting function:	yes
Function to save totals:	yes
Vibration-free weighing (Animal weighing program):	yes


KERN UFN600K200IPM



Pallet scale with stainless steel load support (IP67) and stainless steel display device (IP65), with EC type approval [M]

Piktogramme

STANDARD



OPTION



FACTORY

