

## Han 12Q-MI-CRT- Hybrid



Image is for illustration purposes only. Please refer to product description.

Part number	09 12 012 3006
Specification	Han 12Q-MI-CRT- Hybrid
HARTING eCatalogue	<a href="https://b2b.harting.com/09120123006">https://b2b.harting.com/09120123006</a>

### Identification

Category	Inserts
Series	Han <sup>®</sup> Q
Identification	Hybrid

### Version

Termination method	Crimp termination
Gender	Male
Size	3 A
Number of contacts	8
Number of signal contacts	4
Number of power contacts	4
PE contact	Yes

Details	Please order crimp contacts separately.
	4x Han E <sup>®</sup>
	4x Han D <sup>®</sup>
Details	Please order data or coding element separately.
Details	Please contact your local HARTING subsidiary for selection of suitable angled hood or housing in case of application with data element.

### Technical characteristics

Conductor cross-section	0.14 ... 2.5 mm <sup>2</sup> Signal
	0.14 ... 4 mm <sup>2</sup> Power
Conductor cross-section	AWG 26 ... AWG 14 Signal
	AWG 26 ... AWG 12 Power
Rated current (signal)	10 A



Pushing Performance  
Since 1945

## Technical characteristics

Rated voltage (signal)	250 V
Rated impulse voltage (signal)	4 kV
Pollution degree (signal)	3
Rated current (power)	20 A
Rated voltage (power)	600 V
Rated impulse voltage (power)	6 kV
Pollution degree (power)	3
Insulation resistance	$>10^{10} \Omega$
Limiting temperature	-40 ... +125 °C
Mating cycles	$\geq 500$

## Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

## Commercial data

Packaging size	10
Net weight	9.4 g
Country of origin	China



**Pushing Performance**  
Since 1945

## Commercial data

European customs tariff number 85389099

eCl@ss 27440205 Contact insert for industrial connectors