



AMP

TE Internal #: 567200-3

Applicators, Mechanical Feed, Tape, Cross Section - Photograph / Crimped Samples / Capability Study

[View on TE.com >](#)

Application Tooling > Applicators



Applicator Feed Type: **Mechanical**

Applicator & Product Style: **Tape**

Service Options: **Capability Study, Crimped Samples, Cross Section - Photograph**

Features

Other

Applicator Feed Type	Mechanical
Applicator & Product Style	Tape
Service Options	Capability Study, Crimped Samples, Cross Section - Photograph

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part

numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-324577-0
TERMINAL,PIDG SPD FLG 12-10 6



TE Part # 640917-2
RECEPT,PIDG FASTON 22-18 187



TE Part # 640931-2
RECEPT,PIDG FASTON 16-14 110



TE Part # 52957-3
TERMINAL,PG SPR SPD 16-14 10



TE Part # 640909-2
RCPT,PIDG FASTON 22-18 205



TE Part # 184268-2
RCPT,PIDG FASTON 187 LIF 22-18



TE Part # 2-31425-2
TERMINAL,BUDG R 26-22 2



TE Part # 53829-2
TERMINAL,PG SPR SPD 24-20 4



TE Part # 53833-2
TERMINAL,SOLIS SPR SPD 16-14 8



TE Part # 640911-2
RECEPT,PIDG FASTON 22-18 205



TE Part # 640919-2
RECEPT,PIDG FASTON 16-14 187



TE Part # 640925-2
RECEPT,PIDG FASTON 22-18 110



TE Part # 640915-2
RECEPT,PIDG FASTON 16-14 205



TE Part # 55675-2
RECEPT,PIDG FASTON 22-18 250



TE Part # 640921-2
RECEPT,PIDG FASTON 22-18 110



TE Part # 696018-2
RCPT,PIDG FASTON 22-18 205,LIF



TE Part # 696153-2
TERM, WIRE PIN, PIDG, 22-16, T&R



TE Part # 3-31173-3
BUDG R 22-16COMM 22-18MIL 5/16



TE Part # 2-31159-1
DG R 22-16 COMM 22-18 MIL 6



TE Part # 2-31161-1
DG R 22-16 COMM 22-18 MIL 10

Customers Also Bought



TE Part #66259-2
MALE CONTACT ASSY. (L.P.)



TE Part #2-520403-2
ULTRA-FAST 187 ASY REC 22-18 TPBR



TE Part #217885-6
CRIMPER, WIRE "F"



TE Part #2150041-2
OCEAN_2.0_Applicator-E-110F180F



TE Part #2151168-1
OCEAN_2.0_Applicator-S-090F102F



TE Part #2151314-1
OCEAN_2.0_Applicator-S-110F155F



TE Part #2837605-1
OCEAN-2.0-APPLICATOR-S-112O160F



TE Part #C17298-000
WP-381064-10-9



TE Part #466178-1
HDM EMPO062F140FT



TE Part #466779-6
APPL,HDM 5SAPR176D G

Documents

Product Drawings

[APPL,HDM,TAPE 9CB W/O DIES G](#)

English

[APPL,HDM,TAPE 9CB W/O DIES G](#)

English

Datasheets & Catalog Pages

[TE_APPLICATORS_CATALOG](#)

English



Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English