



**Product:** [74030E](#)

DataTuff Ind SPE 40mGb 26AWG SO SF/UTP PVC

## Product Description

DataTuff Ind SPE 40mGb 26AWG SO SF/UTP PVC

## Technical Specifications

### Product Overview

Suitable Applications:	Tight space cabinet, machine building, 1 single pair Ethernet up to 600 MHz
------------------------	---

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	No. of Pairs
26	Solid	BC - Bare Copper	1

Conductor Count:	2
------------------	---

#### Insulation

Material	Nominal Diameter
PP - Polypropylene	1.3 mm

#### Color Chart

Color
Natural & Natural/Blue

#### Outer Shield

Type	Material	Coverage [%]
Tape	Bi-Laminate (Alum+Poly)	100%
Braid	Tinned Copper (TC)	80%

#### Outer Jacket

Material	Nominal Diameter
PVC - Polyvinyl Chloride	4.10 mm

### Construction and Dimensions

Min Elongation at Breakof Conductors:	8 %
Min Elongation at Breakof Insulation:	100 %
Min Elongation at Breakof Jacket:	100 MPa
Min Tensile Strength of Jacket:	10.3 MPa

### Electrical Characteristics

#### Conductor DCR

Max. Conductor DCR	Max DCR Unbalanced Between Pairs [%]
145 Ohm/km at 20°C	2 %

#### Capacitance

Max. Capacitance Unbalance
----------------------------

160 pF/100m

Dielectric Strength:	2 kVac/1 min
Insulation Resistance:	5000 MOhm*km
Insulation Resistance (Cond to Cond):	5000 MOhm*km
Insulation Resistance (Cond to Screen):	5000 MOhm*km

#### Impedance

##### Nominal Characteristic Impedance

100 Ohm

#### High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	3.1 dB/100m
4 MHz	5.6 dB/100m
10 MHz	8.7 dB/100m
20 MHz	12.3 dB/100m
30 MHz	15.1 dB/100m
100 MHz	27.8 dB/100m
600 MHz	70.7 dB/100m

#### High Frequency

Frequency [MHz]	Min. RL (Return Loss) [dB]	Min. TCL [dB]	Min. ELTCTL [dB]
1 MHz	20 dB	40 dB	40 dB
4 MHz	23 dB	40 dB	28 dB
10 MHz	25 dB	35 dB	20 dB
20 MHz	25 dB	30.5 dB	14 dB
30 MHz	23.5 dB	27.8 dB	10.5 dB
100 MHz	19 dB	20 dB	5 dB
600 MHz	15.6 dB	8.3 dB	5 dB
1000 MHz			

#### Voltage

##### Non-UL Voltage Rating

300 V

#### Temperature Range

Operating Temp Range:	-20°C To +80°C
-----------------------	----------------

#### Mechanical Characteristics

Max Dielectric Shrinkage:	5 %
Dielectric Shrinkage Description:	Shrinkage of Insualtion (100+/ <sup>2</sup> CX1hr)/150mm
Cold Bend Test:	No Crack
Hygroscopicity:	Weight increasing not exceed 1% (for 3hrs)
Wicking:	The filter paper shall not wet (for 6 hrs)
IRM 902 Mineral Oil Resistance Test:	At 70C° x 4hr- Tensile Strength: ≥ 60% of Original Elongation at break:≥ 60% of Original
UV Resistance 720h per UL1581:	(300h) Tensile Strength (Mpa) - 85% of original, Elongation at break (%) - 85% of original

#### Standards

UL AWM Style Compliance:	AWM 2095
CSA AWM Compliance:	AWM I A/B
ISO/IEC Compliance:	IEC 61156-12, UL 758

#### Flammability, LSOH, Toxicity Testing

C(UL) Flammability:	FT2
IEC Flammability:	IEC 60332-1

#### Part Number

#### Variants

Item #	Color	Put-Up Type	Length
74030E 0101000	Black	Reel	1,000 ft

74030E-C500	Blue, Light	Reel	500 m
74030E 0061000	Blue, Light	Reel	1,000 ft
74030E-C1000	Blue, Light	Reel	1,000 m

## History

Update and Revision:	Revision Number: 0.54 Revision Date: 09-09-2021
----------------------	---

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.