




Connectors > Automotive Connectors > Data Connectivity Systems > Data Connectivity Housings



Connector & Housing Type: **Housing for Male Terminals**

Connector & Keying Code: **A**

Connector System: **Cable-to-Cable**

Number of Positions: **4**

Centerline (Pitch): **5.3 mm [.21 in]**

Features

Product Type Features

Connector & Housing Type	Housing for Male Terminals
Connector System	Cable-to-Cable
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	4
---------------------	---

Body Features

Connector & Keying Code	A
Cable Exit Angle	180°

Contact Features

Contact Type	Pin
--------------	-----

Termination Features

Termination Method to Wire & Cable	Crimp (Standard)
------------------------------------	------------------

Mechanical Attachment

--	--



Panel Attachment Style	Rear Mount
Mating Retention	With
Connector Mounting Type	Panel Mount

Housing Features

Housing Color	Water Blue
Centerline (Pitch)	5.3 mm [.21 in]

Usage Conditions

Operating Temperature (Max)	105 °C [221 °F]
Cable Type	Coax
Operating Temperature Range	-40 – 105 °C [-40 – 221 °F]

Operation/Application

Shielded	Yes
Circuit Application	Power & Signal

Other

Dielectric Material	PBT
---------------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold: Pb (.11% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products

will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 776363-1
SEALING PLUG, SZ 16 CAVITY



TE Part # 2292862-1
AS16 BACKSHELL, 4P CAP, SMOOTH EXIT, MC



TE Part # 776441-1
AS 16, EXTRACTION TOOL



TE Part # 2338211-1
CAP PIN ASSY, 4P, W2W, SEALED COAX



TE Part # 2338212-1
PLUG SOCKET ASSY, 4P, W2W, SEALED COAX




TE Part # 2355843-1
1POS, COAX, SOC HSG ASSY, SLD




TE Part # 2355844-1
1POS, PIN DIA 2.5, HDR ASSY, 180DEG



TE Part # 2356408-1
4P, COAX, HDR ASSY, 180DEG, COD A, SHORT



TE Part # 2362356-1
MATE-AX, M TO F, RTK031, 500MM




TE Part # 2362356-2
MATE-AX, M TO F, RTK031, 1000MM



TE Part # 2362356-3
MATE-AX, M TO F, RTK031, 1500MM



TE Part # 2362356-4
MATE-AX, M TO F, RTK031, 3000MM



TE Part # 2362356-5
MATE-AX, M TO F, RTK031, 5000MM



TE Part # 2362359-1
MATE-AX M TO F, DACAR 462, 500MM



TE Part # 2362359-2
MATE-AX M TO F, DACAR 462, 1000MM



TE Part # 2362359-3
MATE-AX M TO F, DACAR 462, 1500MM



Customers Also Bought



Documents

Product Drawings

[CAP PIN ASSY, 4P, FLANGE, SEALED COAX](#)

English

[CAP PIN ASSY, 4P, FLANGE, SEALED COAX](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2339729-1_1.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2339729-1_1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2339729-1_1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English