

MODEL MM7000-2D ThermoBarScan

Waterproof ThermoBarScan thermometer with 1D & 2D Barcode Scanner

FEATURES

A handheld logging thermometer with integral barcode scanner, for recording product location/identity along with time, date and temperature. This thermometer also has built-in Bluetooth communication for data transmittal to PC

- *** °C / °F switchable
- *** Resolution of 0.1° to 1000° autoranging
- *** Switchable thermocouple types K / T / J / R / N / E / S
- *** Infra-Red sensor compatibility
- *** Full retention of thermocouple type and temperature scale
- *** User configurable Auto Switch Off capability
- *** Overrange / Open circuit sensor indication
- *** Low battery indication
- *** IP65 casing complete with protective rubber boot
- *** Integral Barcode reader for 1D and 2D barcode formats
- *** Built in Bluetooth communications
- *** Free Downloadable software

SPECIFICATION

Environmental

AMBIENT OPERATING RANGE	:	0 to 50 °C
STORAGE TEMPERATURE RANGE	:	-20 to 50 °C
HUMIDITY	:	0 to 70% R.H.

ELECTRICAL

MEASUREMENT RANGES	:	K	-200 to 1372 °C
		T	-200 to 400 °C
		J	-200 to 1200 °C
		R	0 to 1767 °C
		N	-200 to 1200 °C
		E	-200 to 1000 °C
		S	0 to 1767 °C
THERMOCOUPLE TYPES	:	K T J R N E S	
INFRA-RED SENSOR (Exergen K80)	:	K80 -50 to 250 °C	
TEMPERATURE SCALES	:	°C / °F	
ACCURACY @23°C	:	+/- 0.1% OF READING +/- 0.2 °C	
CHARACTERISING ACCURACY	:	LESS THAN 0.05 °C	
TEMPERATURE COEFFICIENT	:	0.01% OF READING /°C	
COLD JUNCTION COMPENSATION	:	0.0075 °C/°C	
RESOLUTION	:	0.1° to 1000, 1° ABOVE 1000	

BARCODE

READABLE BARCODES : All UPC/EAN/JAN Codes
 : EAN28 Codes
 : Code39 Code128
 : PDF417
 : QR Code
 : Data Matrix
 : GS1-DataBarTM
 : RSS, RSS Limited, RSS-14
 : RSS-14 Stacked, RSS-Expand

BLUETOOTH

CLASS : Class I
 CONTAINS : FCC Id: S22btmodule-C11

GENERAL

BATTERY : PP3 9V I.E.C. 6F22
 BATTERY LIFE (INTERMITTENT USE) : GREATER THAN 200 HOURS (ALKALINE)
 WEIGHT : 155 gms
 DIMENSIONS : 130 X 70 X 33 mm

Cross-reference for compatible probes

Suitable probes and accessories for use with this instrument

TME PART No	DESCRIPTION	APPLICATION	T/C TYPE
KP05	NEEDLE PROBE	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	K
TP05	NEEDLE PROBE	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	T
KP07	NEEDLE PROBE HEAVY DUTY	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	K
TP07	NEEDLE PROBE HEAVY DUTY	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	T
TP10	SOUS VIDE NEEDLE PROBE	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	T
KM01	LIGHT DUTY M.I. PROBE	GENERAL PURPOSE LIQUID/GAS MEASUREMENT	K
TM01	LIGHT DUTY M.I. PROBE	GENERAL PURPOSE LIQUID/GAS MEASUREMENT	T
KM03	M.I. PROBE	GENERAL PURPOSE LIQUID/GAS MEASUREMENT	K
TM03	M.I. PROBE	GENERAL PURPOSE LIQUID/GAS MEASUREMENT	T
KM04	M.I. PROBE EXTENDED LENGTH	GENERAL PURPOSE LIQUID/GAS MEASUREMENT	K
TM04	M.I. PROBE EXTENDED LENGTH	GENERAL PURPOSE LIQUID/GAS MEASUREMENT	T
KS01	SURFACE BAND PROBE	FAST RESPONSE SURFACE MEASUREMENT	K
TS01-S	DUAL PROBE	FOR SURFACE AND IMMERSION MEASUREMENT	
KS07	SURFACE PROBE	GENERAL PURPOSE SURFACE MEASUREMENT	K
TS04	SURFACE PROBE	GENERAL PURPOSE SURFACE MEASUREMENT	T
KS08	HIGH TEMP SURFACE PROBE	HIGH TEMPERATURE SURFACE MEASUREMENT	K
KS20-S	DUAL PROBE	FOR SURFACE AND IMMERSION MEASUREMENT	K
KA04	AIR TEMPERATURE PROBE	FAST RESPONSE AIR TEMPERATURE PROBE	K
TA04	AIR TEMPERATURE PROBE	FAST RESPONSE AIR TEMPERATURE PROBE	T
TA12	SPATULA PROBE	BETWEEN PACK PROBE	T
KH01	SOCKET IN HANDLE	HANDLE FOR USE WITH PLUG MOUNTED PROBES	K
TH01	SOCKET IN HANDLE	HANDLE FOR USE WITH PLUG MOUNTED PROBES	T
KHA02	PLUG MOUNTED AIR PROBE	FAST RESPONSE AIR TEMPERATURE PROBE	K
THA2	PLUG MOUNTED AIR PROBE	FAST RESPONSE AIR TEMPERATURE PROBE	T
KHM01	PLUG MOUNTED M.I. PROBE	GENERAL PURPOSE LIQUID/GAS MEASUREMENT	K
THM01	PLUG MOUNTED M.I. PROBE	GENERAL PURPOSE LIQUID/GAS MEASUREMENT	T
KHN01	PLUG MOUNTED NEEDLE PROBE	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	K
THN01	PLUG MOUNTED NEEDLE PROBE	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	T
THA12	PLUG MOUNTED SPATULA PROBE	BETWEEN PACK PROBE	T
KHS01	PLUG MOUNTED SURFACE BAND PROBE	FAST RESPONSE SURFACE MEASUREMENT	K
KHS02	PLUG MOUNTED SURFACE PROBE	GENERAL PURPOSE SURFACE MEASUREMENT	K
THS02	PLUG MOUNTED SURFACE PROBE	GENERAL PURPOSE SURFACE MEASUREMENT	T
PKHV1	HVAC KIT	PROBE KIT DESIGNED FOR THE HVAC INDUSTRY	K
PKF1	FOOD KIT	PROBE KIT DESIGNED FOR THE FOOD INDUSTRY	T
PKGP1	GENERAL PURPOSE KIT	PROBE KIT CONTAINING MOST POPULAR PROBES	K
TP01	CORKSCREW PROBE	PROBE DESIGNED FOR CORE TEMPERATURE OF MEAT	T
KPS10	PIPE CLAMP PROBE	PROBE DESIGNED TO BE CLAMPED ONTO PIPES	K
TFS01	FOOD SIMULANT PROBE	SIMULATES THE CORE TEMPERATURE OF FOOD IN HOT OR COLD STORAGE	