



<b>PartNumber</b>	127050-0204
<b>Actuation</b>	Manual
<b>Current Rating</b>	5 A max. per line
<b>Number of Positions</b>	156
<b>Product Group</b>	DLM
<b>Actuating Camshaft Material</b>	Stainless steel, Passivated
<b>Shock</b>	MIL-STD-202 Test Method 213, Condition A (50 G's)
<b>Humidity</b>	MIL-STD-202 Test Method 103, Condition B
<b>Where Sold</b>	Europe, Americas
<b>Component</b>	Connector
<b>Insulator Retainer Material</b>	Stainless steel, Passivated
<b>Insulator Material</b>	Glass filled thermoplastic, UL 94V-0 rated, Color: Black
<b>Insulation Resistance</b>	5000 M ohms min.
<b>Polarization</b>	Polarizing Posts
<b>Footnote</b>	Dimension are shown in mm (inch).
<b>Housing</b>	Metal
<b>Wire Accomodation</b>	#42 AWG to #18 AWG
<b>Dielectric Withstanding Voltage</b>	1200 V AC RMS
<b>Termination Type</b>	Wire Crimp (Contacts sold separately)
<b>Housing Material</b>	Aluminum alloy, nickel plated
<b>Connector Durability</b>	10,000 mating cycles min.
<b>Salt Spray</b>	MIL-STD-202 Test Method 101, Condition B (48 Hours)
<b>Nomenclature</b>	DLM1-156P
<b>Gender</b>	Plug
<b>Crimp Contact Material</b>	Copper alloy, 50 $\mu$ inches gold over 50 $\mu$ inches nickel in mating area, gold flash on balance
<b>Contact Resistance</b>	15 m ohms max. (20 m ohms max. - #32 AWG - #30 AWG contact)
<b>Contact Spacing</b>	2,54 (.100) Square Grid
<b>Contact Retention</b>	8 lbs (35,585 N) min.
<b>Operating Temperature</b>	-55°C to 105°C
<b>Vibration</b>	MIL-STD-202 Test Method 204, Condition C





