



pH FIELD & LAB ELECTRODES

pH ELECTRODES

PHE-1478



pH Electrodes

OMEGA's glass-bodied, refillable (RF), combination pH electrodes are for general purpose laboratory measurements. The inert nature of the glass body allows these electrodes to be used in aqueous and non-aqueous solutions at temperatures up to 110°C (230°F).

The PHE-1479 has a ceramic liquid junction and a saturated potassium chloride electrolyte. This electrolyte is a laboratory standard and is suitable for most measurements. The ceramic junction has a low flat rate that minimizes sample contamination from the potassium chloride solution.

The PHE-1478 has a porous PTFE liquid junction and a saturated potassium chloride electrolyte. The porous PTFE liquid junction provides a stable, non-fouling reference contact ideal for the most demanding applications. This research-grade electrode should be used when the sample has a very low or very high ionic strength, where greases or oils are present, or in biological solutions containing TRIS or large amounts of protein.



PHE-1479, shown smaller than actual size.

SPECIFICATIONS

pH Range: 0 to 14 pH

Temperature Range: -5 to 100°C (23 to 212°F)

Accuracy: ±0.02 pH

Response Time: 95% of reading within 5 seconds

Impedance: 60 MΩ at 25°C (77°F)

Zero Potential: 7.0 ±0.2 pH

Dimensions (L x D): 140 x 12 mm (5.5 x 0.47")



MOST POPULAR MODELS HIGHLIGHTED

To Order (Specify Model Number)

Model No.	Description
PHE-1478	PTFE liquid junction
PHE-1479	Ceramic liquid junction
ES-2207	Reference Book: Handbook of Water and Wastewater Treatment Technologies

Comes with complete operator's manual.

Note: 1 m (3') of cable length is standard; for additional length consult Engineering.
Ordering Example: PHE-1478, PTFE liquid-junction electrode,

Specialty pH Electrodes

These specialty electrodes are designed for surface and subsurface measurements of semi-soft materials. Typical applications include meats, cheese, dairy products, photographic emulsions, and electrophoresis gels.

The PHE-1525 flat style is a refillable combination pH electrode with a polymer body, porous PTFE liquid, and a flat pH glass membrane. It can be used to measure the pH of any moist surface or inverted and used as a "one-drop" electrode. Samples as small as 100 µL are easily measured with this inverted technique.



PHE-1526, shown smaller than actual size.

SPECIFICATIONS

pH Range: 0 to 14 pH

Temperature Range: -5 to 100°C (23 to 212°F)

Accuracy: ±0.02 pH

Response Time: 95% of reading within 5 seconds

Impedance: 60 MΩ at 25°C (77°F)

Zero Potential: 7.0 ±0.2 pH

Dimensions (L x D):

Flat: 140 x 12 mm (5.5 x 0.47")

Spear-Point: 150 x 9.5 mm (5.9 x 0.37")

To Order (Specify Model Number)

Model No.	Description
PHE-1525	Flat-surface pH electrode
PHE-1526	Spear-point pH electrode

Comes with complete operator's manual.

Note: 1 m (3') of cable length is standard; for additional length consult Engineering.

Ordering Example: PHE-1525, flat surface pH electrode,

Options for Combination Electrodes

Suffix	Description
-D	Double junction
-HF	HF fluoride resistant body
-HT	High-temperature reference
-HPH	High-pH glass
-ORP	Redox (ORP) measurement

Options available on PHE-1478, PHE-1479, PHE-1525, PHE-1526, PHE-1523 and PHE-1524 electrodes.

Note: 1 m (3') of cable length is supplied standard; for additional length, consult Engineering.



Laboratory Electrodes

PHE-3216

Laboratory Reference Electrodes



PHE-3216D, shown smaller than actual size.

Laboratory procedures require a separate reference electrode. Several standard methods and techniques for pH measurement and most ion selective electrodes require the use of a "double junction" reference electrode. The PHE-3216 is ideal for such applications. These gel-filled electrodes feature a replaceable porous PTFE liquid junction in a polymer body. They are supplied ready to use with a saturated potassium chloride-silver reference cell. The double junction version uses potassium nitrate as the screening electrolyte, although it can be easily replaced with the electrolyte of your choice. The liquid junction has a large surface area and provides a stable, low-impedance contact to the solution, ensuring fast, accurate measurements. The chemically inert nature of PTFE makes the sensor easy to clean.

SPECIFICATIONS

- pH Range:** 0 to 14 pH
- Temperature Range:** -5 to 100°C (23 to 212°F)
- Response Time:** Stable in 30 seconds
- Resistance:** Less than 1000 Ω
- Liquid Junction:** Porous PTFE
- Electrolytes:** Saturated potassium chloride-silver
- Screening Electrolyte:** 8 molar potassium nitrate
- Dimensions (L x D):** 140 x 12 mm (5.5 x 0.47")

MOST POPULAR MODELS HIGHLIGHTED

To Order (Specify Model Number)


Model No.	Description
PHE-3216	Single-junction pH electrode
PHE-3216D	Double-junction pH electrode

Comes with complete operator's manual.

Ordering Example: PHE-3216, single-junction pH electrode,

Laboratory-Insertable Electrodes


Lab insertables are designed for pH measurement inside narrow vessels. Small volumes in test tubes or solutions in large Erlenmeyer casks can be conveniently measured by one of these responsive electrodes. The PHE-1523 is a glass-bodied, refillable, combination pH electrode. The 5.0" insertion length allows measurement in test tubes or other narrow vessels. This electrode features full-span, fast-response pH glass and high-flow porous PTFE reference junction, making it a must for any laboratory.



PHE-1523, shown smaller than actual size.

SPECIFICATIONS

- pH Range:** 0 to 14 pH
- Temperature Range:** -5 to 100°C (23 to 212°F)
- Accuracy:** ±0.02 pH with proper calibration
- Sodium Error:** 0.05 pH in 0.1 molar Na⁺ ion at 12.8 pH
- Response Time:** 95% in 10 seconds, stable in 30 seconds
- Impedance:** 60 MΩ at 25°C (77°F)
- Zero Potential:** 7.0 ±0.2 pH
- Dimensions (L x D Micro):** 190 x 12 mm (7.5 x 0.47")



PHE-1524, shown smaller than actual size.

The PHE-1524 is a sealed, polymer-bodied, 254 mm (10") long combination pH electrode. The length allows measurements to be made in large, deep flasks or bottles. This sensor has our full-span pH glass and a gel-filled silver chloride reference using the trouble-free porous PTFE liquid junction.

Accessory

Model No.	Description
ES-2186	Reference Book: Environmental Monitoring Handbook



To Order (Specify Model Number)

Model No.	Description
PHE-1523	Glass-body pH electrode
PHE-1524	Polymer-body pH electrode

Comes with complete operator's manual.

Ordering Example: PHE-1523, glass-body pH electrode,



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters