




Model No.: **GP11AF**

Description	: Mercury Free & Lead Free Alkaline High Voltage Multicell
Nominal Voltage	: 6Volts
Nominal Dimensions	: Ø10.22mm×16.5mm
Terminal	: Nickel plated flat contacts - protruded red(+); recessed black (-)
Jacket	: Metal jacket
Internal Connection	: Pressure
Applications	: Remote controller
Average Weight	: 4.0g
Date Code	: Unless otherwise specified, each batteries will carry a numeric year code and analogue month code (+)
Shelf Life	: Not less than 90% of the service capacity within first year storage at 20 ± 2 °C 55 ± 20 %RH
Insulation	: 5MΩ min.
Resistance	
Close Circuit Voltage	: 4.7 Volts (min.)(load resistor 400Ω at 20 ± 2 °C for 0.1 to 2 seconds)
Current Drain	: Under 15mA pulse, 0.5mA continuous
Nominal Service Life	: 74hrs (at 10kΩ load) (to 3.0V at 20 ± 2 °C)
Average Service	: 38mAh(at 10kΩ load)
Capacity	
	(to 3.0V at 20 ± 2 °C)



Unit : mm

Typical Discharge characteristics at 20 ± 2 °C



Cross References:

GP	Eveready	Duracell	Varta
11AF	---	---	---

The information (subject to change without prior notice) contained in this document is for reference only and should not be used as a basis for product guarantee or warranty. For applications other than those described here, please consult your nearest GP Sales and Marketing Office or Distributors.