



Aluform – 04.28 28 11

Aluminium diecast enclosure consisting of lid, seal incl. captive +/- stainless steel screws, base with 4 earthing screws



Dimensions H x W x D (mm)	280 x 280 x 111
Weight (g)	2788
Order number	04.28 28 11
Product type	ALF 04090

- + Aluminium diecast enclosure for MCR and automation technology
- + Prepared for acceptance for front membranes and keypads
- + Rectangular dome sequence in lid and base




Technical Data

Material	DIN EN 1706 EN AC-AISI 12 (Fe)
Colour	Powder coating, RAL 7038, agate grey, special colour on request
Ingress protection	IP 66 to EN 60529, higher protection on request
Impact resistance	7 Joule in reference to EN 60079-0
Temperature range	PU (polyurethane) seal (std.): -40°C to +90°C CR (chloroprene) seal: -40°C to +100°C VMQ (silicone) seal (optional): -60°C to +130°C
Other versions on request	EMC, SBG, SBGL, SWB, Silicone lid seal

Aluform – 04.28 28 11

Number of cable glands

Maximum number of cable glands to DIN 50262*



M	PG	Side	
		A/B	C/D
12	17,25	70	65
16	25,30	30	27
20	27,60	27	24
25	37,95	12	12
32	48,30	8	7
40	60,95	4	4
50	69,00	4	3
63	74,75	3	3
75			
85			

Commercial Data

Country of origin	IN
Pieces per packaging	1
Customs tariff number	85369095
Weight (g)	2788
GTIN	4250157972927

ETIM Classification

ETIM-Class	EC000058
------------	----------

Accessories

Description	Order number
External hinges Set=2 pcs	04.00 00 10
Allen lid screws	12.01 80 01
Lead-sealing screw	12.01 90 01
Lid safety strip Set = 2 pcs	04.00 00 20
External mounting brackets (pair) (set = 2 pcs) for mounting	04.00 00 80
DIN rails TS 15	10.06 10 48
DIN rails TS 35/7,5	10.06 14 81
Mounting plate	10.01 10 71