



BlackFin CT-2523CH Crimp Head

CT-2523CH

Crimps Panduit #26 - 8 AWG (0.14 - 10.0mm²) insulated and non-insulated ferrules and #22 - 12 AWG (0.50 - 4.0mm²) insulated twin wire ferrules - Square profile. Used with the Panduit CT-2500/L Series Battery Hydraulic crimping tool

Specifications

Compatible Connector	Loose Piece F, FSD, FSDX, FSDXL, and FTD series Ferrules
Tool Type	Die Type
Maximum Wire Size (AWG)	#6
Minimum Wire Size (AWG)	#8
Sub Brand	BlackFin
For Use With	CT-2500 , CT-2500/E, CT-2500/L and CT-2500/LE crimp tools
Overall Height (In.)	2
Overall Height (mm)	50
Overall Width (In.)	1
Overall Width (mm)	25
Product Type	Crimp Head
Weight (Kg)	0.4
Weight (lb)	0.92
Crimp Profile	Square
Base Material	Steel
Application	CT-2500, CT-2500/E and CT-2500/L, CT-2500/LE Crimp Tools
Color	Black
Part Features	Self-adjusting crimp die for Insulated and noninsulated ferrules.

Packaging Detail

UPC	61305618127
Std. Pkg. Qty.	1
Std. Pkg. Volume (cf)	0.0366
Std. Ctn. Qty.	0
Std. Ctn. Volume (cf)	0.0000