

TECHNICAL DATA SHEET

Part#: 7210E

Cutters - Medium - Oval/Relieved Head - Semi-Flush
Designed for cutting .050" soft wire leaving no 'pinch' on the wire

The 7210E large Lazer Line[®] round relieved head Semi-flush cutter with a cutting capacity of .008" to .045" soft wire is made of carbon tool steel with induction hardened cutting blades to RHC 63-65. This overall length is 4.75". The CNC machining allows the joint surfaces to be perfect to allow for long life. The dual leaf springs provide a smooth action. It features a ergonomically molded antimicrobial Anti-Static grip (10^{10} ohms/sq surface resistivity) with dual leaf springs.

• Precision Level	★★★★★
• Material	Carbon
• Surface Resistivity	10^{10} ohms/sq
• Shape	Round Relieved Head
• Type of Cut	Optimum Flush
• Cutting Capacity	.008 - .050"
• Blade Angle	14.25°
• Blade Length	.46" (11.5mm)
• Body Width	0.42" (10.5mm)
• Body Height	.25"
• OAL	4.75" (118.75mm)
• Weight (OZ)	3
• UPC	662847009365
• Schedule B	8203.20.60.60
• ECCN	EAR99
• UNSPSC Code	27111511
• Country of Origin	USA
• Group	Medium Cutters - 7000 Series

