



Safety Data Sheet according to (EC) No 1907/2006

Page 1 of 9

PP118 Super Steel 50g SFDN Hard

SDS No. : 441061
V001.2

Revision: 08.06.2015
printing date: 10.11.2020

Replaces version from: 07.10.2014

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

PP118 Super Steel 50g SFDN Hard

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:
Epoxy Hardener

1.3. Details of the supplier of the safety data sheet

Henkel Ltd
Wood Lane End
HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 1442 278000
Fax-no.: +44 1442 278071

ua-productsafety.uk@uk.henkel.com

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):

Skin irritation	Category 2
H315 Causes skin irritation.	
Serious eye irritation	Category 2
H319 Causes serious eye irritation.	

2.2. Label elements

Label elements (CLP):

Hazard pictogram:



Signal word: Warning

Hazard statement: H315 Causes skin irritation.
H319 Causes serious eye irritation.

Precautionary statement: P302+P352 IF ON SKIN: Wash with plenty of water.
Response P337+P313 If eye irritation persists: Get medical advice/attention.

2.3. Other hazards
None if used properly.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
2,4,6-Tris(dimethylaminomethyl)phenol 90-72-2	202-013-9 01-2119560597-27	>= 1- < 3 %	Skin Corr. 1B H314 Acute Tox. 4 H302

For full text of the H - statements and other abbreviations see section 16 "Other information".
Substances without classification may have community workplace exposure limits available.

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation:

Move to fresh air. If symptoms persist, seek medical advice.

Skin contact:

Rinse with running water and soap.

Obtain medical attention if irritation persists.

Eye contact:

Rinse immediately with plenty of running water (for 10 minutes), seek medical attention from a specialist.

Ingestion:

Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

SKIN: Redness, inflammation.

EYE: Irritation, conjunctivitis.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media:

Carbon dioxide, foam, powder

Extinguishing media which must not be used for safety reasons:

None known

5.2. Special hazards arising from the substance or mixture

In the event of a fire, carbon monoxide (CO), carbon dioxide (CO₂) and nitrogen oxides (NO_x) can be released.

5.3. Advice for firefighters

Wear self-contained breathing apparatus.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Avoid contact with skin and eyes.

6.2. Environmental precautions

Do not let product enter drains.

6.3. Methods and material for containment and cleaning up

Scrape up as much material as possible.

Ensure adequate ventilation.

Store in a partly filled, closed container until disposal.

Dispose of contaminated material as waste according to Section 13.

6.4. Reference to other sections

See advice in section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Use only in well-ventilated areas.

Vapours should be extracted to avoid inhalation.

Hygiene measures:

Wash hands before work breaks and after finishing work.

Do not eat, drink or smoke while working.

Good industrial hygiene practices should be observed.

7.2. Conditions for safe storage, including any incompatibilities

Store in a cool, well-ventilated place.

Never allow product to get in contact with water during storage

7.3. Specific end use(s)

Epoxy Hardener

SECTION 8: Exposure controls/personal protection

8.1. Control parameters**Occupational Exposure Limits**Valid for
Great Britain

Ingredient [Regulated substance]	ppm	mg/m ³	Value type	Short term exposure limit category / Remarks	Regulatory list
Limestone 1317-65-3 [CALCIUM CARBONATE, INHALABLE DUST]		10	Time Weighted Average (TWA):		EH40 WEL
Limestone 1317-65-3 [CALCIUM CARBONATE, RESPIRABLE DUST]		4	Time Weighted Average (TWA):		EH40 WEL
Limestone 1317-65-3 [LIMESTONE, RESPIRABLE MARBLE, RESPIRABLE]		4	Time Weighted Average (TWA):		EH40 WEL
Limestone 1317-65-3 [LIMESTONE, TOTAL INHALABLE MARBLE, TOTAL INHALABLE]		10	Time Weighted Average (TWA):		EH40 WEL
Barium sulfate 7727-43-7 [BARIUM SULPHATE, INHALABLE DUST]		10	Time Weighted Average (TWA):		EH40 WEL
Barium sulfate 7727-43-7 [BARIUM SULPHATE, RESPIRABLE DUST]		4	Time Weighted Average (TWA):		EH40 WEL
Silicon dioxide 7631-86-9 [SILICA, AMORPHOUS, INHALABLE DUST]		6	Time Weighted Average (TWA):		EH40 WEL
Silicon dioxide 7631-86-9 [SILICA, AMORPHOUS, RESPIRABLE DUST]		2,4	Time Weighted Average (TWA):		EH40 WEL
Titanium dioxide 13463-67-7 [TITANIUM DIOXIDE, TOTAL INHALABLE]		10	Time Weighted Average (TWA):		EH40 WEL
Titanium dioxide 13463-67-7 [TITANIUM DIOXIDE, RESPIRABLE]		4	Time Weighted Average (TWA):		EH40 WEL
Magnesium carbonate 546-93-0 [MAGNESITE, INHALABLE DUST]		10	Time Weighted Average (TWA):		EH40 WEL
Magnesium carbonate 546-93-0 [MAGNESITE, RESPIRABLE DUST]		4	Time Weighted Average (TWA):		EH40 WEL
Talc (Mg ₃ H ₂ (SiO ₃) ₄) 14807-96-6 [TALC, RESPIRABLE DUST]		1	Time Weighted Average (TWA):		EH40 WEL

Predicted No-Effect Concentration (PNEC):

Name on list	Environmental Compartment	Exposure period	Value				Remarks
			mg/l	ppm	mg/kg	others	
2,4,6-Tris(dimethylaminomethyl)phenol 90-72-2	aqua (freshwater)					0,084 mg/L	
2,4,6-Tris(dimethylaminomethyl)phenol 90-72-2	aqua (marine water)					0,0084 mg/L	
2,4,6-Tris(dimethylaminomethyl)phenol 90-72-2	aqua (intermittent releases)					0,84 mg/L	
2,4,6-Tris(dimethylaminomethyl)phenol 90-72-2	STP					0,2 mg/L	

Derived No-Effect Level (DNEL):

Name on list	Application Area	Route of Exposure	Health Effect	Exposure Time	Value	Remarks
2,4,6-Tris(dimethylaminomethyl)phenol 90-72-2	Workers	Inhalation	Long term exposure - systemic effects		0,31 mg/m ³	
2,4,6-Tris(dimethylaminomethyl)phenol 90-72-2	Workers	Dermal	Long term exposure - systemic effects		0,2 mg/kg bw/day	

Biological Exposure Indices:

None

8.2. Exposure controls:**Respiratory protection:**

Ensure adequate ventilation.

An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area

Filter type: A

Hand protection:

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (NBR; \geq 0.4 mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR; \geq 0.4 mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:

Wear protective glasses.

Skin protection:

Wear suitable protective clothing.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Appearance

liquid

white

Odor

ammoniacal

Odour threshold

No data available / Not applicable

pH	No data available / Not applicable
Initial boiling point	No data available / Not applicable
Flash point	No data available / Not applicable
Decomposition temperature	No data available / Not applicable
Vapour pressure	No data available / Not applicable
Density	1,76 g/cm ³
()	
Bulk density	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Solubility (qualitative)	Insoluble
(Solvent: Water)	
Solidification temperature	No data available / Not applicable
Melting point	No data available / Not applicable
Flammability	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Explosive limits	No data available / Not applicable
Partition coefficient: n-octanol/water	No data available / Not applicable
Evaporation rate	No data available / Not applicable
Vapor density	No data available / Not applicable
Oxidising properties	No data available / Not applicable

9.2. Other information

No data available / Not applicable

SECTION 10: Stability and reactivity

10.1. Reactivity

Polymerises in presence of water.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

No decomposition if used according to specifications.

10.5. Incompatible materials

See section reactivity

10.6. Hazardous decomposition products

carbon oxides.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

General toxicological information:

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation 1272/2008/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

Oral toxicity:

This material is considered to have low toxicity if swallowed.
Ingestion of large quantities may cause liver or kidney damage.

Inhalative toxicity:

Inhalation of vapors in high concentration may cause irritation of respiratory system
Methanol released during polymerisation of RTV silicones is toxic by inhalation. It is also highly flammable

Skin irritation:

Causes skin irritation.

Eye irritation:

Causes serious eye irritation.

Acute oral toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
2,4,6-Tris(dimethylaminomethyl)phenol 90-72-2	Acute toxicity estimate (ATE)	1.378 mg/kg	oral			Expert judgement
2,4,6-Tris(dimethylaminomethyl)phenol 90-72-2	LD50	1.378 - 1.968 mg/kg			rat	OECD Guideline 401 (Acute Oral Toxicity)

Acute dermal toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
2,4,6-Tris(dimethylaminomethyl)phenol 90-72-2	LD50		dermal		rat	

Skin corrosion/irritation:

Hazardous components CAS-No.	Result	Exposure time	Species	Method
2,4,6-Tris(dimethylaminomethyl)phenol 90-72-2	corrosive	4 h	rabbit	OECD Guideline 404 (Acute Dermal Irritation / Corrosion)

Respiratory or skin sensitization:

Hazardous components CAS-No.	Result	Test type	Species	Method
2,4,6-Tris(dimethylaminomethyl)phenol 90-72-2	not sensitising	Buehler test	guinea pig	OECD Guideline 406 (Skin Sensitisation)

SECTION 12: Ecological information**General ecological information:**

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation 1272/2008/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

Cured Loctite products are typical polymers and do not pose any immediate environmental hazards.

Precautions required with respect to Environmental Hazards of articles in which this product is used should be considered.

12.1. Toxicity**Ecotoxicity:**

Do not empty into drains / surface water / ground water.

Hazardous components CAS-No.	Value type	Value	Acute Toxicity Study	Exposure time	Species	Method
2,4,6- Tris(dimethylaminomethyl)ph enol 90-72-2	LC50	153 mg/l	Fish	96 h	Brachydanio rerio (new name: Danio rerio)	ISO 7346-1 (Determination of the Acute Lethal Toxicity of Substances to a Freshwater Fish [Brachydanio rerio Hamilton- Buchanan (Teleostei, Cyprinidae)])

12.2. Persistence and degradability

Persistence and Biodegradability:

The product is not biodegradable.

12.3. Bioaccumulative potential / 12.4. Mobility in soil

Mobility:

Cured adhesives are immobile.

Bioaccumulative potential:

No data available.

Hazardous components CAS-No.	LogKow	Bioconcentration factor (BCF)	Exposure time	Species	Temperature	Method
2,4,6- Tris(dimethylaminomethyl)ph enol 90-72-2	-0,66				21,5 °C	EPA OPPTS 830.7550 (Partition Coefficient, n- octanol / H ₂ O, Shake Flask Method)

12.5. Results of PBT and vPvB assessment

Hazardous components CAS-No.	PBT/vPvB
2,4,6-Tris(dimethylaminomethyl)phenol 90-72-2	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

12.6. Other adverse effects

No data available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product disposal:

Dispose of in accordance with local and national regulations.

Contribution of this product to waste is very insignificant in comparison to article in which it is used

Disposal of uncleaned packages:

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Disposal must be made according to official regulations.

Waste code

08 04 09 waste adhesives and sealants containing organic solvents and other dangerous substances

The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

SECTION 14: Transport information

- 14.1. UN number**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.2. UN proper shipping name**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.3. Transport hazard class(es)**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.4. Packaging group**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.5. Environmental hazards**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.6. Special precautions for user**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code**
not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

VOC content < 3 %
(1999/13/EC)

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

H302 Harmful if swallowed.
H314 Causes severe skin burns and eye damage.

Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.