


ELECTRICAL TEST:



- 1.100% OPEN SHORT MIS WIRE TEST
- 2.CONTACT RESISTANCE:5 OHM MAX
- 3.INSULATION RESISTANCE:5M OHM MIN
- 4.HI-POT TEST:DC 300V/10ms
- 5.PASS 8K@60Hz TEST

CONSUMER ITEM	LENGTH(mm)
3M	3000±30



PIN Assignment

P1 HDMI AM P2 HDMI AM



NO.	PART NAME	DESCRIPTION	UNIT
⑥	CABLE	(1/0.34BC*1P+D1/0.254TC+AL-Foil+ADHESIVE-PET)*5C+1/0.254BC*3C+1/0.32BC*1C+AL-Foil+D7/0.16TC+160#/0.12AL BLACK PVC Jacket OD:7.3±0.15mm	m
⑤	MODEL	BLACK 45P PVC molding	xxg
④	SHELL	Silver white aluminum shell	2PCS
③	MODEL	PE,Nature color	xxg
②	Copper foil	Copper foil size:5mm	cm
①	plug	HDMI AM 19P SHELL/PIN:Gold plated & Tinplate	2pcs

				DESCRIPTION	FINISHED PRODUCT'S FIGURE	SCALE	FIT	UNITS: MM	1RD ANGLE
				MODEL NO.		△			
APPROVED	CHECKED	DRAWING	DESIGNED	DRAWING NO.		△			
		YAN	YAN	FINISHING		△	2021/07/09		A1
				MATERIAL		SYM	DATE		REVISION