


# Amphenol®



## Amphe-PD™

Amphenol's Amphe-PD™ series of "RADSOK® enabled" power connectors is a versatile and cost effective solution for your high current interconnect requirements. Available in the compact 3.6mm, 70A rated option and a larger 5.7mm, 120A big brother. The Amphe-PD™ is reintroduced with a new black PBT housing that is more robust and aesthetically pleasing. The Amphe-PD™ series meets RoHS requirements and is UL and IEC finger touch safe. Available in a myriad of configurations for high flex cable, PCB, and busbar mounting. Custom cable assemblies are available.

### Features:

- RADSOK® sizes 5.7mm and 3.6mm
- 120A and 70A rated 2 position connector
- Low profile right angle exit less than ½ inch mated height
- 12 AWG to 4 AWG crimp contact with insulated latching housings
- RADSOK® Socket and pin / silver over nickel plating
- High Temp LCP housing for SMT processing of PCB mount receptacles

Plug Connector with Crimp Terminals	
Part Number	Description
C10-752156-000	BLACK, 3,6MM - AWG 12
C10-752157-000	BLACK, 3,6MM - AWG 8
C10-752158-000	BLACK, 3,6MM - AWG 6
C10-752159-000	BLACK, 3,6MM - AWG 4
C10-752160-000	BLACK, 3,6MM - AWG 8 1500V SPECIAL
C10-752162-000	BLACK, 5,7MM - AWG 4

Receptacle Connectors: PCB, Busbar or Crimp Contacts	
Part Number	Description
C10-752153-001	BUSBAR RECEPTACLE BLACK, 3,6MM
C10-752154-001	PCB SOLDER SMT LCP RECEPTACLE BLACK, 3,6MM - HIGH TEMP
C10-752155-000	PCB SOLDER RECEPTACLE BLACK, 3,6MM
C10-747795-000	PCB RIGHT ANGLE SOLDER RECEPTACLE BLACK, 3,6MM
C10-752161-000	CRIMP RECEPTACLE BLACK, 3,6MM - AWG-8 1500V SPECIAL
C10-752163-000	PCB SOLDER RECEPTACLE BLACK, 5,7MM

**C10-752162-000  
RADSOK® Plug, 5.7mm**

**C10-752163-000  
RADSOK® Receptacle, 5.7mm**

**C10-752160-000  
RADSOK® Plug, 1500V**

**C10-752161-000  
RADSOK® Receptacle, 1500V**

**RADSOK® Amphe-PD Cable Assemblies are Available**

**C10-752158-000  
RADSOK® Plug, 3.6mm**

**C10-752155-000  
RADSOK® Receptacle, 3.6mm**

**C10-747795-000  
RADSOK® Receptacle, 3.6mm**

Notice: Specifications are subject to change without notice. Contact your nearest Amphenol Corporation Sales Office for the latest specifications. All statements, information and data given herein are believed to be accurate and reliable but are presented without guarantee, warranty, or responsibility of any kind, expressed or implied. Statements of suggestions concerning possible use of our products are made without representation or warranty that any such use is free of patent infringement and are not recommendations to infringe any patent. The user should assume that all safety measures are indicated or that other measures may not be required. Specifications are typical and may not apply to all connectors.

For further information on your individual application requirements, contact: Amphenol Corporation

North America:  
Amphenol Industrial Operations  
180 N. Freepoint Drive, Plant 4  
Nogales, AZ 85621  
Tel: (888) 364-9011  
Fax: (520) 285-5134  
Email: tech@amphenol-aio.com

Europe:  
Amphenol Industrial Operations Europe  
Via Barbaiana 5  
1-20020 Lainate (MI) Italy  
Tel: +39 02 93254.204  
Fax: +39 02 93254.444  
Email: info@amphenol-aio.com

Middle East:  
Amphenol Middle East Enterprises FZE  
Office C-37 PO Box 21107  
Ajman Free Zone, UAE  
Tel: +9 716-7422494  
Fax: +9 716-7422941  
Email: jhussain@amphenol-industrial.com

Asia:  
Amphenol Technology (Zhuhai) Co., Ltd.  
No. 63 Xing Han Road, San Zao Town  
Jin Wan District, Zhuhai City, China 519040  
Tel: +86 756-3989760  
Fax: +86 756-3989768  
Email: enquiry@amphenol-aio.com