

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **2180570220**
Status: **Active**
Overview: EXTreme Guardian System
Description: EXTreme Guardian Female-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, Bluntcut Wires, 11.00mm Pitch, Single Row, 2.0m Length, 2 Circuits, Black

Documents:

[Drawing \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|------------------------|--------------------------------|
| Product Family | Cable Assemblies |
| Series | <u>218057</u> |
| Application | Power, Wire-to-Board |
| Assembly Configuration | Single Ended Connector |
| Connector to Connector | EXTreme Guardian-to-Pigtail |
| Overview | <u>EXTreme Guardian System</u> |
| Product Name | EXTreme Guardian |
| Type | Discrete Wire Assembly |
| UPC | 195842766563 |


Physical

| | |
|--------------------------------|----------------------|
| Cable Length | 2.0m |
| Circuits (Loaded) | 2 |
| Color - Resin | Black |
| Gender | Female-Pigtail |
| Lock to Mating Part | Yes |
| Material - Metal | Copper Alloy |
| Material - Plating Mating | Gold |
| Material - Plating Termination | Tin |
| Material - Resin | PBT |
| Net Weight | 410.000/g |
| Number of Rows | 1 |
| Packaging Type | Bag |
| Pitch - Mating Interface | 11.00mm |
| Plating min - Mating | 0.762µm |
| Single Ended | Yes |
| Termination Interface: Style | Crimp or Compression |
| Wire Size AWG | 6 |
| Wire/Cable Type | UL 10669 |

Material Info

Reference - Drawing Numbers

| | |
|---------------|----------------|
| Sales Drawing | 2180570205-000 |
|---------------|----------------|



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

218057 Series

Mates With

151035 EXTreme Guardian Power Right-Angle PCB Header, 151053 EXTreme Guardian Power Vertical PCB Header