



- The exclusive two-piece design offers the lowest threading force in the industry
- Small head height permits more efficient use of space in compact areas
- Average 14% lighter than one-piece ties
- Excellent for critical applications such as aircraft design
- Releaseable for bundle modifications prior to tensioning and cutoff

Part Number:	SST3S-C0
Product Family:	<i>Sta-Strap</i> ® Cable Ties - Releasable - Weather Resistant Nylon 6.6
Product Line:	Two Piece Nylon Cable Ties
RoHS Compliancy Status:	Compliant
Part Description:	Cable Tie, Releasable, 11.0", Standard cross section
Product Type:	Cable Ties
Material:	Weather Resistant Nylon 6.6
Color:	Black
CSA Certified:	Yes
UL Listed (File #E56854):	No
UL Recognized (File #E56854):	Yes
Length (In.):	11.0

Length (mm):	279
Width (In.):	.180
Width (mm):	4.6
CE Compliant:	Yes
Cross Section:	Standard
Head Height (In.):	.250
Head Height (mm):	6.4
Head Width (In.):	.310
Head Width (mm):	7.9
Locking Style:	Releasable
Material Flammability Rating:	UL94V-2
Max. Bundle Diameter (In.):	3.00
Max. Bundle Diameter (mm):	76
Max. Continuous Use Temperature:	185°F (85°C)
Min. Loop Tensile Strength (Lbs.):	50
Min. Loop Tensile Strength (N):	222
Std. Pkg. UOM:	PK
Thickness (In.):	.048
Thickness (mm):	1.2

Tool: GTS, GTSL, GS2B, GTH, GS4H, PTS, PTH, PPTS, STS2, STH2

UOM: PC

Std. Pkg. Qty.: 100

Min. Order Qty.: 100