



Connectors > Circular Connectors > Standard Circular Connectors

Connector System: **Wire-to-Board, Wire-to-Wire**Number of Positions: **12**Sealable: **Yes**Connector & Contact Terminates To: **Printed Circuit Board**Contact Current Rating (Max): **2 A**

Features

Product Type Features

Product Type	Connector
Connector System	Wire-to-Board, Wire-to-Wire
Sealable	Yes
Connector & Contact Terminates To	Printed Circuit Board
Circular Connector Type	Plug
Shell Type	Plastic

Configuration Features

Number of Positions	12
Number of Power Positions	0
Number of Signal Positions	12
Contacts Preloaded	Yes

Body Features

Shell Base Material	PBT
Circular Connector Insulation Material Type	Polyamide 66 GF25

Contact Features

Contact Current Rating (Max)	2 A
Reverse Gender	Yes
Contact Layout Arrangement	Circular
Circular Connector Contact Type	Socket



Mechanical Attachment

Polarization Code	A
Mating Alignment Type	Keyed
Mating Retention	With

Housing Features

Circular Connector Shell Size	12
-------------------------------	----

Dimensions

Wire Size	.25 mm ²
-----------	---------------------

Usage Conditions

IP Water Sealing Level	7
IP Dust Sealing Level	6
Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]

Operation/Application

Circuit Application	Signal
Shielded	No

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JAN 2022 (223) SVHC > Threshold: Pb (3% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # CAT-C73765-M1G
M12 Panel Mount Solder Cups



TE Part # CAT-C73765-M1H
M12 Panel Mount PCB



TE Part # CAT-C73765-M1F
M12 Panel Mount Wire



TE Part # 6-2271122-2
M12, MALE, A CODE, R/A, 12P, PG9 (AU)



TE Part # 6-2271134-2
M12, MALE PNL, A CODE, SOLDER REAR, 12P, (AU)

Customers Also Bought



TE Part #7-2834006-2
2P MRPK CONN_RD/BK




TE Part #T4130012121-000
M12 Panel Mount Solder Cups



TE Part #T4140012121-000
M12, REAR MOUNT, MALE, A, 12P, SOLDER PCB



TE Part #8-1879337-8
CPF 0603 20K 1% 50PPM 1K RL



TE Part #1-284391-2
TERMI-BLOK PCB SIDE ENTRY STAC



TE Part #6-2271110-2
M12, MALE, A CODE, 12P, PG9 (AU)



TE Part #87113-4
04 MODI HDR SRST .156CL



TE Part #1571262-4
SWITCH,TACTILE,SMT,W/BOSS,T&R

Documents

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_6-2271128-2_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_6-2271128-2_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_6-2271128-2_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[M8 / M12 Connector System Catalog](#)

English

Product Specifications

[Product Specification](#)

English