


For mating dimensions see MIL-DTL-38999 Series III

Reference MIL-STD-1560 for insert arrangement details. For non-MS arrangements consult Amphenol.

PANEL THICKNESS
.067-.130
[1,71-3,30]

PCB Stickout .150
[3,81]

For rear shell features and accessories see MIL-DTL-38999 Series III




NOTE:
-DRAWING NOT TO SCALE
-DIMENSIONS SUBJECT TO CHANGE
-DIMENSIONS ARE IN INCHES [MM]

PROPERTY OF AMPHENOL AEROSPACE. ALL RIGHTS RESERVED.

Meets applicable requirements of MIL-DTL-38999
Base Material: Aluminum
Plating: AP-93

AMPHENOL CORPORATION <small>40-60 DELAWARE AVENUE SIDNEY, N.Y. 13838</small>			
RECEPTACLE Electrical Connector TVS07			U
<small>SIZE</small> C	<small>CAGE CODE</small> 77820	<small>CODED NUMBER</small> TVS07DS-21-35P(P15)	<small>REV</small> X1
SHEET 1 OF 1			

Insert Arrangement



No. of Contacts	79
Contact Size	22D
Wire Size	28, 26, 24, 22

Shell Size	21
Arrangement	35
Service Rating	M
Test Current	5 AMPS

NOTE:
 -DRAWING NOT TO SCALE
 -DIMENSIONS SUBJECT TO CHANGE
 -DIMENSIONS ARE IN INCHES [MM]

PROPERTY OF AMPHENOL AEROSPACE. ALL RIGHTS RESERVED.

AMPHENOL CORPORATION <small>40-60 DELAWARE AVENUE SIDNEY, N.Y. 13838</small>			
RECEPTACLE Electrical Connector TVS07			U
SIZE C	CAGE CODE 77820	CODED NUMBER TVS07DS-21-35P(P15)	REV X1
SHEET 1 OF 1			