



AMP | Heavy Duty Sealed Connector Series, MATEnet

TE Internal #: 9-2334942-1

Automotive Connector Caps & Covers, Cover, Cable Exit Angle 180°, Black, PA 66, -40 – 257 °F [-40 – 125 °C], Heavy Duty Sealed Connector Series

[View on TE.com >](#)

Connectors > Automotive Connectors > Automotive Connector Accessories > Automotive Connector Caps & Covers



Protection & Strain Relief Accessory Type: **Cover**

Cable Exit Angle: **180°**

Primary Product Color: **Black**

Primary Product Material: **PA 66**

Operating Temperature (Max): **125 °C [ 257 °F ]**

**Features**

**Product Type Features**

Protection & Strain Relief Accessory Type	Cover
---	-------

Sealable	No
----------	----

**Body Features**

Cable Exit Angle	180°
------------------	------

Primary Product Color	Black
-----------------------	-------

Primary Product Material	PA 66
--------------------------	-------

**Dimensions**

Compatible Cable Bundle Diameter Range	3.3 mm
--	--------

**Usage Conditions**

Operating Temperature (Max)	125 °C[257 °F]
-----------------------------	----------------

Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]
-----------------------------	----------------------------

**Packaging Features**

Packaging Method	Loose Piece - Bag
------------------	-------------------



## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

### Product Compliance Disclaimer





This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts




 <p>TE Part # 9-2331355-1 HD MATEnet 1+6 REC. HSG ASSY, GRP D</p>	 <p>TE Part # 9-2331355-2 HD MATEnet 1+6 REC. HSG ASSY, GRP D</p>	 <p>TE Part # 9-2331355-3 HDSENET 1+6 REC. HSG ASSY D</p>	 <p>TE Part # 9-2331355-4 HDSENET 1+6 REC. HSG ASSY D</p>
--	--	--	--



Also in the Series | **Heavy Duty Sealed Connector Series**



Also in the Series | **MATEnet**






Data Connectivity Housings(31)



Other Automotive Connector Accessories(1)



PCB Headers &amp; Receptacles(2)

## Customers Also Bought

TE Part #1563111-1  
COVER,180TE Part #2-1564514-1  
Heavy Duty Sealed Connector Series  
HousingsTE Part #9-2331355-1  
HD MATEnet 1+6 REC. HSG ASSY,  
GRP DTE Part #9-2334935-1  
HD MATEnet 1+6 TAB HSG. ASSY,  
GRP DTE Part #9-2334941-1  
HD MATEnet 1+6 SWS, GRP D

## Documents

### Product Drawings

[HD MATEnet COVER FOR SWS, GRP D](#)

English

[HD MATEnet COVER FOR SWS, GRP D](#)

English

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_9-2334942-1\\_A.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_9-2334942-1\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_9-2334942-1\\_A.3d\\_stp.zip](#)



English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

[Product Specifications](#)

[Application Specification](#)

English