www.vishay.com

Hyperfast Rectifier, 30 A FRED Pt<sup>®</sup> G5



### LINKS TO ADDITIONAL RESOURCES



PRIMARY CHARACTERISTICS					
I <sub>F(AV)</sub>	30 A				
V <sub>R</sub>	600 V				
V <sub>F</sub> at I <sub>F</sub> at 125 °C	1.3 V				
t <sub>rr</sub> (typ.)	22				
I <sub>FSM</sub>	310				
T <sub>J</sub> max.	175 °C				
Package	TO-247AD 3L				
Circuit configuration	Single				

#### **FEATURES**

- Hyperfast and optimized Q<sub>rr</sub>
- · Best in class forward voltage drop and switching losses trade off
- Optimized for high speed operation
- 175 °C maximum operating junction temperature FREE
- · Polyimide passivation
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

### **DESCRIPTION / APPLICATIONS**

Featuring a unique combination of low conduction and switching losses, this rectifier is the right choice for soft switched and resonant converters, as well as medium frequency hard switching converters. This device is specifically designed to improve efficiency of high speed LLC output rectification stages of EV / HEV battery charging stations and high frequency stages of UPS applications.

### **MECHANICAL DATA**

Case: TO-247AD 3L Molding compound meets UL 94 V-0 flammability rating Terminal: matte tin plated leads, solderable per J-STD-002

ABSOLUTE MAXIMUM RATINGS								
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS				
Repetitive peak reverse voltage	V <sub>RRM</sub>		600	V				
Average rectified forward current	I <sub>F(AV)</sub>	T <sub>C</sub> = 117 °C, D = 0.50	30					
Non-repetitive peak surge current	I <sub>FSM</sub>	$T_{C}$ = 25 °C, $t_{p}$ = 10 ms, sine wave both anodes, (1) and (3) connected	310	А				
Repetitive peak forward current	I <sub>FRM</sub>	T <sub>C</sub> = 117 °C, D = 0.50, f = 20 kHz	60					
Operating junction and storage temperature	T <sub>J</sub> , T <sub>Stg</sub>		-55 to +175	°C				

<b>ELECTRICAL SPECIFICATIONS</b> (T <sub>J</sub> = 25 °C unless otherwise specified)								
PARAMETER	SYMBOL TEST CONDITIONS				MAX.	UNITS		
Breakdown voltage, blocking voltage	$V_{BR}, V_{R}$	I <sub>R</sub> = 100 μA	600	-	-			
Forward voltage	VF	I <sub>F</sub> = 30 A	-	1.6	2.1	V		
Forward voltage	٧F	I <sub>F</sub> = 30 A, T <sub>J</sub> = 125 °C	-	1.3	-			
Reverse leakage current	I <sub>R</sub>	V <sub>R</sub> = V <sub>R</sub> rated	-	-	20			
neverse leakage current		$T_J = 125 \text{ °C}, V_R = V_R \text{ rated}$	-	-	500	μA		
Junction capacitance	CT	V <sub>R</sub> = 200 V	-	36	-	pF		
Series inductance	Ls	Measured to lead 5 mm from package body	-	8	-	nH		

Revision: 26-May-2021 Document Number: 96901 For technical questions within your region: DiodesAmericas@vishay.com, DiodesAsia@vishay.com, DiodesEurope@vishay.com THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishav.com/doc?91000



RoHS COMPLIANT HALOGEN

VS-A5PX3006L-N3



www.vishay.com

## **Vishay Semiconductors**

DYNAMIC RECOVERY CHARACTERISTICS (T <sub>J</sub> = 25 °C unless otherwise specified)								
PARAMETER	SYMBOL	TEST CO	MIN.	TYP.	MAX.	UNITS		
		$I_F = 1.0 \text{ A}, \text{ d}I_F/\text{d}t = 10$	0 A/µs, V <sub>R</sub> = 30 V	-	22	-		
Reverse recovery time	t <sub>rr</sub>	T <sub>J</sub> = 25 °C		-	39	-	ns	
		T <sub>J</sub> = 125 °C		-	50	-		
Peak recovery current		T <sub>J</sub> = 25 °C	I <sub>F</sub> = 20 A dI <sub>F</sub> /dt = 1000 A/μs V <sub>R</sub> = 400 V	-	14	-	A nC	
Feat recovery current	I <sub>RRM</sub>	T <sub>J</sub> = 125 °C		-	24	-		
Poverse recovery charge	0	T <sub>J</sub> = 25 °C		-	253	-		
Reverse recovery charge	Q <sub>rr</sub>	T <sub>J</sub> = 125 °C		-	785	-		
Boyoroo rocoyory timo	+	T <sub>J</sub> = 25 °C	I <sub>F</sub> = 30 A dI <sub>F</sub> /dt = 1000 A/μs V <sub>R</sub> = 400 V	-	41	-	20	
Reverse recovery time	t <sub>rr</sub>	T <sub>J</sub> = 125 °C		-	56	-	ns	
Pack recover a surrent		T <sub>J</sub> = 25 °C		-	16	-	Α	
Peak recovery current	I <sub>RRM</sub>	T <sub>J</sub> = 125 °C		-	27	-	A	
		T <sub>J</sub> = 25 °C		-	306	-		
Reverse recovery charge	Q <sub>rr</sub>	T <sub>J</sub> = 125 °C		-	952	-	nC	

THERMAL - MECHANICAL SPECIFICATIONS								
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS		
Thermal resistance, junction-to-case	R <sub>thJC</sub>		-	-	1.1	°C/W		
Waight			-	5.5	-	g		
Weight			-	0.2	-	oz.		
Mounting torque			6 (5)	-	12 (10)	kgf · cm (lbf · in)		
Maximum junction and storage temperature range	T <sub>J</sub> , T <sub>Stg</sub>		-55	-	175	°C		
Marking device		Case style: TO-247AD 3L	A5PX3006L					




Fig. 1 - Typical Forward Voltage Drop Characteristics





Fig. 2 - Typical Values of Reverse Current vs. Reverse Voltage



600

V<sub>R</sub> - Reverse Voltage (V) Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage

300

400

500

0

100

200




Fig. 4 - Maximum Allowable Case Temperature vs. Average Forward Current




Fig. 5 - Average Power Loss vs. Average Forward Current





Fig. 6 - Thermal Impedance Z<sub>thJC</sub> - Characteristics

Revision: 26-May-2021 3 For technical questions within your region: DiodesAmericas@vishay.com, DiodesAsia@vishay.com, DiodesEurope@vishay.com THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000





www.vishay.com

Fig. 7 - Typical Reverse Recovery Time vs. dl<sub>F</sub>/dt




Fig. 8 - Typical Reverse Recovery Charge vs. dl<sub>F</sub>/dt




Fig. 9 - Typical Reverse Recovery Current vs. dl<sub>F</sub>/dt





Fig. 10 - Typical Reverse Recovery Time vs. dl<sub>F</sub>/dt








Fig. 12 - Typical Reverse Recovery Current vs. dl<sub>F</sub>/dt

Revision: 26-May-2021

4

Document Number: 96901

For technical questions within your region: <u>DiodesAmericas@vishay.com</u>, <u>DiodesAsia@vishay.com</u>, <u>DiodesEurope@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>








Fig. 13 - Reverse Recovery Waveform and Definitions

#### Notes

- <sup>(1)</sup> di<sub>F</sub>/dt rate of change of current through zero crossing
- (2) I<sub>RRM</sub> peak reverse recovery current
- (3)  $t_{rr}$  reverse recovery time measured from  $t_0$ , crossing point of negative going  $I_F$ , to point  $t_{10\%}$ , 0.1  $I_{RRM}$
- $^{(4)}$   $Q_{rr}$  area under curve defined by  $t_0$  and  $t_{10\ \%}$

$$Q_{rr} = \int_{t_0}^{t_{10\%}} I(t) dt$$

 $^{(5)}$  di<sub>(rec)</sub>M/dt - peak rate of change of current during t<sub>b</sub> portion of t<sub>rr</sub>

### **ORDERING INFORMATION TABLE**

Device code	VS-	Α	5	Р	x	30	06	L	-N3
	1	2	3	4	5	6	7	8	9
	1 -	Visl	hay Sen	nicondu	ctors pro	oduct			
	2 - Circuit configuration								
	A = single diode, 2 anodes <b>3</b> - 5 = Fred generation 5								
	4 - Package:								
		P =	TO-247	' packag	je				
	5 -	X =	hyperfa	st recov	very				
	6 - Current rating (30 = 30 A)								
	7 - Voltage rating (06 = 600 V)								
	8 -	Pac	kage: L	= long l	ead (TC	)-247AE	D)		
	9 -			ntal digit gen-free		-complia	ant, and	totally I	ead (Pb)

ORDERING INFORMATION (Example)						
PREFERRED P/N QUANTITY PER TUBE MINIMUM ORDER QUANTITY PACKAGING DESCRIPTION						
VS-A5PX3006L-N3	25	500	Antistatic plastic tube			

LINKS TO RELATED DOCUMENTS						
Dimensions www.vishay.com/doc?95626						
Part marking information www.vishay.com/doc?95007						
Revision: 26-May-2021	5 Document Number: 96901					

For technical questions within your region: <u>DiodesAmericas@vishay.com</u>, <u>DiodesAsia@vishay.com</u>, <u>DiodesEurope@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



TO-247AD 3L

#### **DIMENSIONS** in millimeters and inches



View B

SYMBOL	MILLIN	IETERS	INCHES		NOTES
STIVIBOL	MIN.	MAX.	MIN.	MAX.	NOTES
А	4.65	5.31	0.183	0.209	
A1	2.21	2.59	0.087	0.102	
A2	1.50	2.49	0.059	0.098	
b	0.99	1.40	0.039	0.055	
b1	0.99	1.35	0.039	0.053	
b2	1.65	2.39	0.065	0.094	
b3	1.65	2.34	0.065	0.092	
b4	2.59	3.43	0.102	0.135	
b5	2.59	3.38	0.102	0.133	
с	0.38	0.89	0.015	0.035	
c1	0.38	0.84	0.015	0.033	
D	19.71	20.70	0.776	0.815	3
D1	13.08	-	0.515	-	4

(2, 52, 51) (4) Section C - C, D - D, E - E

SYMBOL	MILLIN	IETERS	INC	HES	NOTES
STNIBOL	MIN.	MAX.	MIN.	MAX.	NOTES
D2	0.51	1.30	0.020	0.051	
E	15.29	15.87	0.602	0.625	3
E1	13.46	-	0.53	-	
е	5.46	BSC	0.215	5 BSC	
ØК	0.2	0.254		0.010	
L	19.81	20.32	0.780	0.800	
L1	3.71	4.29	0.146	0.169	
ØР	3.56	3.66	0.14	0.144	
Ø P1	-	6.98	-	0.275	
Q	5.31	5.69	0.209	0.224	
R	4.52	5.49	0.178	0.216	
S	5.51	BSC	0.217	' BSC	

#### Notes

<sup>(1)</sup> Dimensioning and tolerancing per ASME Y14.5M-1994

(2) Contour of slot optional

- <sup>(3)</sup> Dimension D and E do not include mold flash. These dimensions are measured at the outermost extremes of the plastic body
- (4) Thermal pad contour optional with dimensions D1 and E1
- <sup>(5)</sup> Lead finish uncontrolled in L1
- (6) Ø P to have a maximum draft angle of 1.5 to the top of the part with a maximum hole diameter of 3.91 mm (0.154")
- <sup>(7)</sup> Outline conforms to JEDEC<sup>®</sup> outline TO-247 with exception of dimension A min., D, E min., Q min., S, and note 4

 Revision: 06-Mar-2020
 1
 Document Number: 95626

 For technical questions within your region: DiodesAmericas@vishay.com, DiodesAsia@vishay.com, DiodesEurope@vishay.com
 DiodesEurope@vishay.com

 THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000



Vishay

# Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.