

USB 2.0 Cable Male Type A to B


multicomp PRO

**RoHS
Compliant**



Specifications:

Insulation resistance	: DC 300V 10MΩ
Contact resistance	: 3Ω Max
Dielectric strength	: 100V AC/Minute, 1mA.
Printing	: USB 2.0 CABLE, 28AWG×1P+28AWG×2C
Connector Type A	: USB Type A Plug
Connector Type B	: USB Type B Plug
Cable Length	: 1.8m / 3m / 4.5m
USB Standard	: USB 2.0
Jacket Colour	: White



No.	Parts	Specification Standard	QTY
1	Cable	USB 2.0 28AWG(BC*1P)+28AWG (BC*2C) +AB AL-MG JACKET : PVC/white OD : 3.8 ±0.2mm	1
2	USB A Type	USB A /M Type, The Pin Gold Plating 3μ", the shell for Nickel Plating	1
3	USB B Type	USB B /M Type, The Pin Gold Plating 3μ", the shell for Nickel Plating	1
4	Outer Mold	Shore 88A PVC Color: White	2

Part Number Table

Description	Length	Part Number
USB 2.0 Cable, Type A to B Plug, White	1800 ±30mm	11.99.8819
	3000 ±50mm	11.99.8831
	4500 ±100mm	11.99.8841

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicomp PRO