



### Overview

Amphenol RF offers a number of 50 ohm front mount bulkhead SMA and RP-SMA jacks designed to accommodate ultraminiature micro-coax cable types. These jacks are available in the straight crimp configuration and feature a threaded coupling mechanism for secure mating.

The front mount bulkhead SMA and RP-SMA jacks can be fastened inside of a panel or enclosure to provide additional security for sensitive systems. This is aided by a tamper resistant design and the flexibility of the micro-coax cables.

These connectors are part of a robust portfolio of ultraminiature products suitable for applications such as drones, test and measurement equipment, industrial automation and inspection, and Bluetooth and cellular technology.

### Features and Benefits

- Reliable electrical performance up to 6 GHz
- Threaded coupling mechanism for secure mating
- Vibration and tamper resistant design
- Ideal for applications with space constraints

### Applications

- Antennas
- Base Stations
- Drones
- Test and Measurement Equipment
- Industrial Automation and Inspection
- Bluetooth and Cellular technology
- WLAN

### Amphenol RF

Four Old Newtown Road  
Danbury, CT 06810

For more information visit [www.amphenolrf.com](http://www.amphenolrf.com)  
or call 800.627.7100

### Ordering Information

#### SMA Front Mount Bulkhead Jacks for Micro-Coax Cable

Part Number	Description
901-10753	SMA Straight Front Mount Jack Bulkhead, 0.81 mm
901-10754	SMA Straight Front Mount Jack Bulkhead, 1.13 mm
901-10755	SMA Straight Front Mount Jack Bulkhead, 1.32 mm
901-10756	SMA Straight Front Mount Jack Bulkhead, 1.37 mm

#### RP-SMA Front Mount Bulkhead Jacks for Micro-Coax Cable

Part Number	Description
901-10769	RP-SMA Straight Front Mount Jack Bulkhead, 0.81 mm
901-10770	RP-SMA Straight Front Mount Jack Bulkhead, 1.13 mm
901-10771	RP-SMA Straight Front Mount Jack Bulkhead, 1.32 mm
901-10772	RP-SMA Straight Front Mount Jack Bulkhead, 1.37 mm
901-10773	RP-SMA Straight Front Mount Jack Bulkhead, RG-178

# Amphenol® RF

## Technical Specifications

### Electrical

Impedance		50Ω
Frequency Range		DC - 6 GHz
Voltage Rating		166 RMS Max Continuous
Dielectric Withstanding Voltage		500 VRMS Min
VSWR (Return Loss)	DC – 3 GHz	1.3 Max
	3 – 6 GHz	1.4 Max
Insulation Resistance		5000 MΩ Min
Center Contact Resistance		3.0 mΩ Min
Outer Contact Resistance		2.0 mΩ Min

### Environmental

Temperature Range		-65°C to +165°C
RoHS Compliance		Compliant with Exemption 6C

### Mechanical

Mating Cycles		500 Min
Coupling Mechanism		Threaded

### Materials

Body		Brass, Gold Plating
Contact		Beryllium Copper, Gold Plating
Insulator		PTFE, Natural

*Note: Technical specifications are typical and may vary by specific part number. Please see component drawing.*

## Amphenol RF

Four Old Newtown Road  
Danbury, CT 06810

For more information visit [www.amphenolrf.com](http://www.amphenolrf.com)  
or call 800.627.7100