

## Product information

# 77 02 130

## Electronics Diagonal Cutter

DIN ISO 9654



- Round head, with small bevel
- Cutting edge hardness approx. 62 HRC
- For fine cutting work, e.g. in electronics and fine mechanics
- Load-optimised for a more direct feel when working
- Sturdy, zero-backlash box joint
- Low-friction double spring for gentle and even opening
- The polish or mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Cutters additionally laser hardened, cutter hardness at least 60 HRC
- Narrow sleeves pulled up to the head of the pliers enable the tool to be guided securely and comfortably, also between thumb and index finger
- Ball bearing chrome steel, oil hardened




### General

|             |                            |
|-------------|----------------------------|
| Article No. | 77 02 130                  |
| EAN         | 4003773039341              |
| Head        | mirror polished            |
| Handles     | with multi-component grips |
| Weight      | 124 g                      |
| Dimensions  | 130 x 60 x 18 mm           |
| Standard    | DIN ISO 9654               |
| Reach       | no                         |
| RohS        | no                         |

### Technical details

|  |              |
|--|--------------|
| Cutting capacities medium hard wire (diameter) | Ø 1.5 mm     |
| Cutting capacities hard wire (diameter)        | Ø 0.8 mm     |
| Cutting capacities soft wire (diameter)        | Ø 0.3 – 2 mm |
| Jaw length (B)                                 | 18 mm        |
| Jaw thickness (joint) (D)                      | 9.5 mm       |
| Head width (A)                                 | 15 mm        |





| <b>Classification</b> |   |
|-----------------------|---|
| eCl@ss 5.1.4          | 21040302                                  |
| ETIM 5.0              | EC000165                                  |
| ETIM 6.0              | EC000165                                  |
| proficl@ss 6.0        | AAA949c004                                |
| UNSPSC 13.1           | 27112114                                  |
| <b>Spare Parts</b>    |   |
| 35 99 01              | Spare spring for electronics pliers, (2x) |

*technical change and errors excepted*