

## Product information

# 77 12 115 ESD

## Electronics Diagonal Cutter ESD

DIN ISO 9654 DIN EN 61 340-5



- Round head, with bevel and lead catcher - no uncontrolled loss of cut wire ends
- Cutting edge hardness approx. 62 HRC
- For fine cutting work, e.g. in electronics and fine mechanics
- Electrically discharging handles - dissipative
- Sturdy, zero-backlash box joint
- Low-friction double spring for gentle and even opening
- The mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Handles with two-colour multi-component grips black/grey
- Ball bearing chrome steel, oil hardened




### General

|             |                              |
|-------------|------------------------------|
| Article No. | 77 12 115 ESD                |
| EAN         | 4003773025108                |
| Head        | mirror polished              |
| Handles     | with multi-component grips   |
| Weight      | 70 g                         |
| Dimensions  | 115 x 66 x 17 mm             |
| Standard    | DIN ISO 9654 DIN EN 61 340-5 |
| Reach       | no                           |
| RohS        | no                           |

### Technical details

|  |                |
|--|----------------|
| Cutting capacities medium hard wire (diameter) | Ø 1.2 mm       |
| Cutting capacities hard wire (diameter)        | Ø 0.6 mm       |
| Cutting capacities soft wire (diameter)        | Ø 0.3 – 1.6 mm |
| Jaw length (B)                                 | 14 mm          |
| Jaw thickness (joint) (D)                      | 7.5 mm         |
| Head width (A)                                 | 11 mm          |
| ESD  | yes            |



| <b>Classification</b> |   |
|-----------------------|---|
| eCl@ss 5.1.4          | 21040302                                  |
| ETIM 5.0              | EC000165                                  |
| ETIM 6.0              | EC000165                                  |
| proficl@ss 6.0        | AAA949c004                                |
| UNSPSC 13.1           | 27112149                                  |
| <b>Spare Parts</b>    |   |
| 35 99 01              | Spare spring for electronics pliers, (2x) |

*technical change and errors excepted*

