

Product information

77 52 115

Electronics Diagonal Cutter

DIN ISO 9654



- Pointed, flat head, with small bevel
- Cutting edge hardness approx. 60 HRC
- For fine cutting work, e.g. in electronics and fine mechanics
- Load-optimised for a more direct feel when working
- Sturdy, zero-backlash box joint
- Low-friction double spring for gentle and even opening
- The polish or mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Cutters additionally laser hardened, cutter hardness at least 60 HRC
- Narrow sleeves pulled up to the head of the pliers enable the tool to be guided securely and comfortably, also between thumb and index finger
- Ball bearing chrome steel, oil hardened




General

Article No.	77 52 115
EAN	4003773040750
Head	mirror polished
Handles	with multi-component grips
Weight	65 g
Dimensions	115 x 66 x 17 mm
Standard	DIN ISO 9654
Reach	no
RohS	no

Technical details

Cutting capacities medium hard wire (diameter)	Ø 0.8 mm
Cutting capacities hard wire (diameter)	Ø 0.5 mm
Cutting capacities soft wire (diameter)	Ø 0.3 – 1 mm
Jaw length (B)	14 mm
Jaw thickness (joint) (D)	7.5 mm
Head width (A)	11 mm



Classification	
eCl@ss 5.1.4	21040302
ETIM 5.0	EC000165
ETIM 6.0	EC000165
proficl@ss 6.0	AAA949c004
UNSPSC 13.1	27112114
Spare Parts	
35 99 01	Spare spring for electronics pliers, (2x)

technical change and errors excepted

