

Product Datasheet

Product code: **E5141.CR.BG**

Product type: High Precision Cutters

Made in: Switzerland

Description: The 5141 is a high precision cutter belonging to the small oval cutter family. This type of geometry provides excellent resistance, while the 5141 head dimensions allow to access small areas. The flush cutting edge is suitable to perform clean cuts with some tolerances. The 5141 is equipped with an ESD Ergo-tek handle which allows an excellent grip, suitable to environments and to components susceptible to electrostatic discharge. The blades are hardened to 67HRC hardness.

Head description: Small Oval

Cutting edges: Flush

Cutting capacity: soft wire 0.10-1.20 mm (38-17 AWG)

Body material: High carbon-chromium low alloy steel (100Cr6)

Body finishing: Sandblasted

Handle material: Ergo-tek - Thermoplastic Elastomer + PP compound

Picture:



Dimensions:

OAL (A)	125.0 mm – 4.921 inch
Width	60.0 mm – 2.362 inch
Height	21.0 mm – 0.827 inch

Head dimensions:

Width (C)	10.0 mm – 0.394 inch
Thickness (D)	6.4 mm – 0.252 inch
B	9.0 mm – 0.354 inch
F	0.7 mm – 0.028 inch

