

Product information

79 62 125 ESD

Precision Electronics Side Cutter ESD

DIN ISO 9654 DIN EN 61 340-5




- Electrically discharging handles - dissipative
- Pointed head
- With lead catcher - no uncontrolled loss of cut wire ends
- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Very precisely ground and sharp cutting edges with very small bevels for exact cutting on delicate electronic components; also available without bevel for flush cutting
- Precision cutting edges additionally induction-hardened, cutting edge hardness approx. 64 HRC
- Approx. 20% lighter than conventional electronics pliers
- Bolted joint with carefully manufactured joint surfaces for even, low-friction movement throughout the entire opening range
- Smooth-running double spring for a gentle and even opening
- Ergonomically optimised multi-component handles
- Ball bearing chrome steel, forged, multi stage oil-hardened

General

| | |
|-------------|------------------------------|
| Article No. | 79 62 125 ESD |
| EAN | 4003773065166 |
| Pliers | burnished |
| Head | polished |
| Handles | with multi-component grips |
| Weight | 58 g |
| Dimensions | 125 x 49 x 19 mm |
| Standard | DIN ISO 9654 DIN EN 61 340-5 |
| Reach | no |
| RohS | no |

Technical details

| | |
|--|----------------|
| Cutting capacities medium hard wire (diameter) | Ø 0.8 mm |
| Cutting capacities soft wire (diameter) | Ø 0.1 – 1.3 mm |
| Jaw length (B) | 11 mm |
| Jaw thickness (joint) (D) | 6.5 mm |
| Head width (A) | 11 mm |
| ESD | yes |



| Classification | |
|-----------------------|--|
| eCl@ss 5.1.4 | 21040302 |
| ETIM 5.0 | EC000165 |
| ETIM 6.0 | EC000165 |
| proficl@ss 6.0 | AAA949c004 |
| UNSPSC 13.1 | 27112114 |
| Accessories | |
| 00 11 V79 | Material catcher for 79 02 / 22 125 ESD, |

technical change and errors excepted

