

Product information

92 51 01

Precision Tweezers




- For particularly demanding precision work: tough and highly resistant to corrosion
- Handcrafted: polished edges and an excellent matt, scratch-free and non-reflective surface
- For the electronics industry, watchmakers, jewellers, laboratories with biological and medical applications in moderately aggressive chemical environments
- High-quality premium stainless steel: high temperature resistance and excellent corrosion resistance to most chemicals, salts and acids
- Ideally suited for microscopic work, precision handling, repairs, manufacturing electronic components, as well as other general applications; tips are guaranteed to have perfect symmetry and balance
- Also available as a set (92 00 02)
- Premium stainless steel

General

| | |
|-------------------|--------------------------|
| Article No. | 92 51 01 |
| EAN | 4003773085126 |
| Material | premium stainless steel |
| Gripping surfaces | smooth gripping surfaces |
| Weight | 15 g |
| Dimensions | 120 x 10 x 11 mm |
| Reach | no |
| RohS | no |

Technical details

| | |
|---------------------|----------------------|
| Tips width (A) | 0.13 mm |
| Tips width (B) | 1.9 mm |
| Corrosion-resistant | yes |
| | no |
| VDE tested | no |
| sectors | Industry electronics |



Classification

| | |
|----------------|------------|
| eCl@ss 5.1.4 | 21040500 |
| ETIM 5.0 | EC000182 |
| ETIM 6.0 | EC000182 |
| proficl@ss 6.0 | EAB696c019 |

technical change and errors excepted