


Metal 'D' Tin and Dimple Connectors- IDC



Features

- Tin and dimple shells
- Black insulators and IDC crimp back shell
- Selective gold / tin plated contacts
- Available with or without 4-40 UNC threads
- Design allows use with standard back shells

Specifications


Electrical

Working Current : 1.5 A
 Test Voltage : 1,000 V
 Insulation Resistance : 5,000 MΩ
 Contact Resistance : Less than 10 mΩ
 Temperature Range : -55°C to +125°C

Material

Insulator : Glass filled polyester black
 Shell : Stamped steel tin plated
 Contacts : Copper alloy
 Contact Plating : 1.5 micron Tin and 0.2 micron gold

Diagram



Dimension Table

Ways	A	B	C	H	H2
9	25	30.8	12.5	15.5	18.5
15	33.3	39.1			
25	47	53			
37	63.5	69.3			

H = Height after crimping
 H2 = With strain relief

Dimensions : Millimetres

Part Number Table

Description	Part Number
9 Way Plug - Unthreaded	MH10551
15 Way Plug - Unthreaded	MH10552
25 Way Plug - Unthreaded	MH10553
37 Way Plug - Unthreaded	MH10554
9 Way Socket - Unthreaded	MH10575
15 Way Socket - Unthreaded	MH10576
25 Way Socket - Unthreaded	MH10577
37 Way Socket - Unthreaded	MH10578
9 Way Plug - 4-40 UNC Threaded	MH10567
15 Way Plug - 4-40 UNC Threaded	MH10568
25 Way Plug - 4-40 UNC Threaded	MH10569
37 Way Plug - 4-40 UNC Threaded	MH10570
9 Way Socket - 4-40 UNC Threaded	MH10591
15 Way Socket - 4-40 UNC Threaded	MH10592
25 Way Socket - 4-40 UNC Threaded	MH10593
37 Way Socket - 4-40 UNC Threaded	MH10594

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.