


Grove - Triple Color E-Ink Display 2.13"



The Grove - Triple Color E-Ink Display 2.13" is a screen that can still be displayed after power off, we call it E-Paper(electronic paper) or E-Ink. The display is a TFT active matrix electrophoretic display, with interface and a reference system design. The 2.13 inch active

area contains 212x104 pixels, and has 1-bit white/black and 1-bit red full display capabilities.

Due to the advantages like ultra low power consumption, wide viewing angle, clear display without electricity, it is an ideal choice for applications such as shelf label, industrial instrument, and so on.



[<https://www.seeedstudio.com/Grove-Triple-Color-E-Ink-Display-2-13-p-2889.html>]

Feature

- High contrast
- High reflectance
- Ultra wide viewing angle
- Ultra low power consumption
- On-chip display RAM

Specification

Item	Value
Supply voltage	3.3V / 5V
Operating temperature	0 ~ 40°C
Storage temperature	-25 ~ 60°C
Humidity range	40~70%RH
Display resolution	212(H) x 104(V) pixel
DPI	111
Interface	UART
Baud rate with Arduino	230400



Attention

Frequent continuous refresh will cause irreparable damage to E-Ink. It is recommended that the refresh interval be greater than 180s.

Pinout





Figure 1. *pinout*

Platforms Supported



Getting Started

Play With Arduino

Hardware

Materials required

Seeeduino V4.2



Base Shield



Get ONE Now

[<https://www.seeedstudio.com/Seeeduino-V4.2-p-2517.html>]

Get ONE Now

[<https://www.seeedstudio.com/Base-Shield-V2-p-1378.html>]



Note

1 Please plug the USB cable gently, otherwise you may damage the port. Please use the USB cable with 4 wires inside, the 2 wires cable can't transfer data. If you are not sure about the wire you have, you can click [here](https://www.seeedstudio.com/Micro-USB-Cable-48cm-p-1475.html) [<https://www.seeedstudio.com/Micro-USB-Cable-48cm-p-1475.html>] to buy

2 Each Grove module comes with a Grove cable when you buy. In case you lose the Grove cable, you can click [here](https://www.seeedstudio.com/Grove-Universal-4-Pin-Buckled-20cm-Cable-%285-PCs-pack%29-p-936.html) [<https://www.seeedstudio.com/Grove-Universal-4-Pin-Buckled-20cm-Cable-%285-PCs-pack%29-p-936.html>] to buy.

- **Step 1.** Plug Grove - Base Shield into Seeeduino.
- **Step 2.** Connect Seeeduino to PC via a USB cable.
- **Step 3.** Download the code, please refer to the software part.

- **Step 4.** Connect the Grove - Triple Color E-Ink Display 2.13" to port **UART** of Grove-Base Shield.




Figure 2. connect



Note

This module communicate with the control board via the UART interface. If you use the Atmega328p board like Arduino UNO or Seeduino V4.2, you need to unplug this module before download the code, because there is only one hardware serial port. If this module occupied the UART port, the download program cannot use the serial port. However if you use SAMD board, like seeeduino Lotus, Arduino Mega, there are two or more hardware serial port available. So there is no need to unplug the module before download.

Software



Attention

If this is the first time you work with Arduino, we strongly recommend you to see [Getting Started with Arduino](#)

[https://wiki.seeedstudio.com/Getting_Started_with_Arduino/] before the start.

- **Step 1.** Download the **Demo code** [https://github.com/Seeed-Studio/Grove_Triple_Color_E-Ink_2.13/tree/master/examples/Eink_factory_code_213] from Github.
- **Step 2.** Open the **Eink_factory_code_213.ino** file with your Arduino IDE.
- **Step 3.** Upload the demo. If you do not know how to upload the code, please check **How to upload code** [https://wiki.seeedstudio.com/Upload_Code/].



Success

If everything goes well, you will see the display flickering, and the the display will show the seeed logo

DIY




Figure 4. Image2LCD configuration

Please check the corresponding option as shown above.

1. Output file type -> *.C
 2. Scan mode -> Horizon Scan
 3. BitsPixel -> monochrome
 4. Max Width and Height -> 104 x 212
 5. Reverse color: Whether you need to check this option is based on the effect you need to display. For more detail please check the **Table 1** below.
- **Step 3.** After you configure the above options, you only need to click the **Save** button in the upper left corner to generate the corresponding image array. Then replace the the factoryCode array with your own image array.

Display		White background Black image		Black background White image
Black Array	Image(Reversed)	Image(Reversed)	Image	Image
Red Array	00	FF	00	FF

Table 1. Array display effect

Note

- a. **00** means all elements in the array are 0x00, actually you need 2756 0x00
- b. **FF** means all elements in the array are 0xFF, actually you need 2756 0xFF
- c. **Image(Reversed)** means you need to check the **Reverse color** option in the **Step 2(Figure 4)**
- b. **Image** means do not check the **Reverse color** option in the **Step 2(Figure 4)**

Tip

*Make a 2756 0x00 or 0xFF array?
Don't worry, we feel your pain, you can just click the 0x00.c and 0xFF.c file and copy into your code.*

[0x00.c](https://files.seeedstudio.com/wiki/Grove-Triple_Color_E-Ink_Display_2.13/res/00.c) [https://files.seeedstudio.com/wiki/Grove-Triple_Color_E-Ink_Display_2.13/res/00.c]

[0xff.c](https://files.seeedstudio.com/wiki/Grove-Triple_Color_E-Ink_Display_2.13/res/ff.c) [https://files.seeedstudio.com/wiki/Grove-Triple_Color_E-Ink_Display_2.13/res/ff.c]

We consider the original state is full screen white. When updating the image, the black array is updated first, then the red array is updated, and the image of the red array overwrites the black image.

This display is 104 x 212, so there are $104 \times 212 = 22048$ pixels, each pixel is controlled by one bit. The element in the array is a two-digit hexadecimal number, like **0xF0**. Convert **0xF0** to a binary number we will get **1111 0000**. A pixel with a value of 1 will display white, and a pixel with a value of 0 will display the color of the corresponding array (red or black). Which means each element in the image array controls 8 pixels. So you need an array of $22048/8 = 2756$ elements.

Step 4. Download the code into your arduino, then you plug the display module into the arduino board. After blinking for a while, you will see the pattern you set.

Schematic Online Viewer



Resources

- **[Zip]** Grove - Triple Color E-Ink Display 2.13" Eagle Files
[https://files.seeedstudio.com/wiki/Grove-Triple_Color_E-Ink_Display_2.13/res/Triple_Color_E-Ink_Display_2_13.zip]
- **[PDF]** E-paper 2.13inch Datasheet
[https://files.seeedstudio.com/wiki/Grove-Triple_Color_E-Ink_Display_2.13/res/E-paper_2.13_inch.pdf]

Tech Support

Please do not hesitate to submit the issue into our [forum](https://forum.seeedstudio.com/) [<https://forum.seeedstudio.com/>] .



[https://www.seeedstudio.com/act-4.html?utm_source=wiki&utm_medium=wikibanner&utm_campaign=newproducts]