
# 1-2336678-6 - ACTIVE

TE Internal #: 1-2336678-6 PCB Mount Header, Right Angle, Wire-to-Board, 6 Position, .079 in [2 mm] Centerline, Fully Shrouded, Tin, Surface Mount, Signal, Natural

#### View on TE.com >

Connectors > PCB Connectors > PCB Headers & Receptacles



Connector System: Wire-to-Board

Number of Positions: 6

Number of Rows: 1

Centerline (Pitch): 2 mm [.079 in ]

PCB Mount Orientation: Right Angle

#### Features

#### Product Type Features

connectivity

| Connector System                  | Wire-to-Board         |
|-----------------------------------|-----------------------|
| Header Type                       | Fully Shrouded        |
| Connector & Contact Terminates To | Printed Circuit Board |
| PCB Connector Assembly Type       | PCB Mount Header      |
| Configuration Features            |                       |
| Number of Positions               | 6                     |
| Number of Rows                    | 1                     |
| PCB Mount Orientation             | Right Angle           |
| Electrical Characteristics        |                       |
| Operating Voltage                 | 50 VAC                |
| Body Features                     |                       |
| Connector Profile                 | Standard              |
| Connector Code                    | A                     |
| Primary Product Color             | Natural               |

**C** For support call+1 800 522 6752

#### 1-2336678-6

PCB Mount Header, Right Angle, Wire-to-Board, 6 Position, .079 in [2 mm] Centerline, Fully Shrouded, Tin, Surface Mount, Signal, Natural



#### **Contact Features**

| Contact Mating Area Plating Material Thickness | 2 µm[80 µin]  |
|--|---------------|
| Contact Mating Area Plating Material Finish    | Bright        |
| PCB Contact Termination Area Plating Material  | Tin           |
| Contact Mating Area Plating Material           | Tin           |
| Contact Type                                   | Pin           |
| Contact Current Rating (Max)                   | 2 A           |
| Termination Features                           |               |
| Termination Method to Printed Circuit Board    | Surface Mount |
| Mechanical Attachment                          |               |
| Mating Alignment Type                          | Polarization  |
| Mating Retention                               | With          |
| PCB Mount Retention Type                       | Pegs          |
| Connector Mounting Type                        | Board Mount   |
| Mating Alignment                               | With          |
| PCB Mount Retention                            | With          |

### Housing Features

| Housing Material            | Nylon - GF                  |
|-----------------------------|-----------------------------|
| Centerline (Pitch)          | 2 mm[.079 in]               |
| Dimensions                  |                             |
| PCB Thickness (Recommended) | .8 – 1.6 mm[.031 – .063 in] |
| Usage Conditions            |                             |
| Operating Temperature Range | -40 – 105 °C[-40 – 221 °F]  |
| Operation/Application       |                             |
| Shielded                    | No                          |
| Circuit Application         | Signal                      |
| Industry Standards          |                             |
| Glow Wire Rating            | Glow Wire                   |
| Agency/Standard             | VDE                         |
| Approved Standards          | UL E28476                   |
| UL Flammability Rating      | UL 94V-0                    |
| Packaging Features          |                             |

#### 1-2336678-6

PCB Mount Header, Right Angle, Wire-to-Board, 6 Position, .079 in [2 mm] Centerline, Fully Shrouded, Tin, Surface Mount, Signal, Natural



| Packaging Type   | Tape & Reel  |
|--|--|
| <b>Product Compliance</b><br>For compliance documentation, visit the product page on TE.com> |  |
| EU RoHS Directive 2011/65/EU   | Compliant  |
| EU ELV Directive 2000/53/EC  | Compliant  |
| China RoHS 2 Directive MIIT Order No 32, 2016  | No Restricted Materials Above Threshold  |
| EU REACH Regulation (EC) No. 1907/2006   | Current ECHA Candidate List: JUNE 2022<br>(224)<br>Candidate List Declared Against: JUN 2020<br>(209)<br>SVHC > Threshold:<br>Not Yet Reviewed |
| Halogen Content  | Low Halogen - Br, Cl, F, I < 900 ppm per<br>homogenous material. Also BFR/CFR/PVC<br>Free  |
| Solder Process Capability  | Not reviewed for solder process capability   |

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

## **Compatible Parts**




## **Customers Also Bought**

#### 1-2336678-6

PCB Mount Header, Right Angle, Wire-to-Board, 6 Position, .079 in [2 mm] Centerline, Fully Shrouded, Tin, Surface Mount, Signal, Natural





## Documents

Product Drawings SGI2.0 RA SMT HDR ASSY 6P,key A,NTL

English

CAD Files

3D PDF

3D

Customer View Model ENG\_CVM\_CVM\_1-2336678-6\_A.2d\_dxf.zip

English

**Customer View Model** 

ENG\_CVM\_CVM\_1-2336678-6\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1-2336678-6\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Product Specifications Application Specification

English

Agency Approvals VDE Certificate

English