

Fiber Optic Sensor Amplifier - Dual output NPN with light compensation

Leon (C

FOACAMPC1NH2

Fiber Optic Sensor Amplifier

Features

- Dual NPN output
- · Automatic light compensation
- · Teaching mode

Applications

- · Industrial automation
- Discrete manufacturing
- · High volume production
- · Automotive manufacturing

- · Customized sensing distance
- Dual digital diplay
- · Adjustable response time
- · Stamping and plastic injection molding
- Packaging
- · Food and Beverage
- · Warehouse automation

Description

The L-com FOACAMPC1NH2 is a high speed, dual (NPN) output fiber optic sensor Amplifier, also referred to as a fiber sensor. Featuring light compensation technology, the amplifier can account for dusty conditions, ensuring accuracy is maintained. Typically mounted to a DIN rail, the unit comes with a adapter for easy mounting to a wall or panel. The easy-to-read dual digital display allows for simultaneous viewing of signal and threshold levels, making for convenient setup and performance at a glance. Fast response time allows for detecting small objects. Used in conjunction with L-com fiber optic sensor cables, the resulting optical sensor is well suited for use in manufacturing and other industrial applications where fast, accurate sensing is critical. The L-com FOACAMPC1NH2 is part of the IoT portfolio of products available from L-com, in-stock and ready to ship. Contact our knowledgeable technical support and sales staff for more information on this, and other IoT products from L-com.

General Specifications

Design Type
Detection Method

Ports Channels

Amplifier Output Selection

Light Source Red Amplifier Output Type

Supply Voltage Cable Length

Compatible Products

(For more information please consult User Guide)

Dual NPN with auto compensation

Light Intensity

2x 2.2mm diameter

2

Light-On / Dark-On

660 nm

Dual NPN

12-24 VDC (± 10%)

2 m

Fiber Optic Sensor Cables

Mechanical Specifications

Length Width Height

Weight Electrical Connection

Mount Type

2.83 in [71.88 mm] 0.41 in [10.41 mm] 1.36 in [34.54 mm] 0.11 lbs [49.9 g]

Flying leads

DIN Rail / Wall Mount

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Fiber Optic Sensor Amplifier - Dual output NPN with light compensation FOACAMPC1NH2




Fiber Optic Sensor Amplifier - Dual output NPN with light compensation



FOACAMPC1NH2

Fiber Optic Sensor Amplifier

Circuit Diagram



Environmental Specifications

Temperature

Operating Range -25 to +55 deg C Storage Range -30 to +70 deg C

Humidity

Operating Relative 35% to 85%

Compliance Certifications (see for current document)

CE Compliance Yes RoHS Compliance Yes

Fiber Optic Sensor Amplifier - Dual output NPN with light compensation from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

For more information, see user manual: https://www.l-com.com/lmages/Downloadables/Manuals/M FOACAMPC1NH2.pdf

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

L-com CAD Drawing

