

MULTI PARAMETER GAS MASS FLOWMETERS

For Clean Gases

FMA6600 Series
Starts at



- ✓ Multi-Drop Capability of Up to 256 Units (for RS485 Option)
- ✓ Stores Calibration Data for Up to 10 Different Gases
- ✓ Supports 10 Different Engineering Units Including User Defined
- ✓ Programmable 12-Digits Totalizer Indicates Total Gas Volume
- ✓ Flow Alarm Limits for High and Low Gas Flow with Relay Output
- ✓ Pressure Alarm (FMA6700) Limits for High and Low Gas Pressure with Relay Output
- ✓ Temperature Alarm (FMA6700) Limits for High and Low Gas Temperature with Relay Output
- ✓ Digital (RS232 or RS485) and Analog Outputs Operate Simultaneously
- ✓ Internal Conversion Factors for Up to 32 Gases

Interface

All features of the FMA6600 and FMA6700 Series flow meters can be accessed via the local four button keypad and LCD. The digital interface operates via RS485 (optional RS232 available) and provides access to applicable internal data including: flow,



FMA6701,
shown actual size.

temperature, and pressure readings, auto zero, totalizer and alarms settings, gas table, conversion factors and engineering units selection, dynamic response compensation and linearization table adjustment.

The analog interface provides 0 to 5 Vdc, 0 to 10 Vdc or 4 to 20 mA outputs for flow, pressure and temperature (jumper selectable).

Auto Zero

The FMA6600 and FMA6700 Series supports automatic sensor zero offset adjustment that can be activated locally via keypad or remotely via digital interface. The auto zero feature requires absolutely no flow through the meter during auto zero process. Provisions are made to either start, stop or save the current auto zero

value via digital commands.

Totalizer

The total volume of the gas is calculated by integrating the actual gas flow rate with respect to time. Both keypad menu and digital interface commands are provided to:

- Set the totalizer to ZERO
- Start the totalizer at a preset flow
- Assign action at a preset total volume
- Start/stop totalizing the flow
- Read totalizer

Totalizer conditions become true, when the totalizer reading and the "Stop at Total" volumes are equal.

Flow Alarm

High and Low gas flow ALARM

limits can be preprogrammed via keypad or remotely via digital interface. ALARM conditions become true when the current flow reading is equal or higher/lower than corresponding values of high and low alarm levels. Alarm action can be assigned with preset delay interval (0 to 3600 seconds) to activate the contact closer (separate for High and Low alarm).

Pressure Alarm (FMA6700 Series)

High and Low gas pressure ALARM limits can be preprogrammed via keypad or remotely via digital interface. Pressure alarm conditions become true when the current pressure reading is equal or higher than corresponding values of high pressure alarm settings or equal or lower than corresponding values of low pressure alarm settings. Alarm action can be assigned to activate the contact closer (separate for High and Low pressure alarm).

Temperature Alarm (FMA6700 Series)

High and Low gas temperature ALARM limits can be preprogrammed via keypad or remotely via digital interface. Temperature alarm conditions become true when the current temperature reading is equal or higher than corresponding values of high temperature alarm settings or equal or lower than corresponding values of low temperature alarm settings. Alarm action can be assigned to activate the contact closer (separate for High and Low temperature alarm).

Engineering Units

The flow set points, measured gas flow and associated totalizer data are scaled directly in engineering units via the front panel keypad or digital interface.

The following units of measure are supported: %F.S., L/min, L/h, mL/min, mL/h, SCFH, SCFM, LbPH, LbPM, User Defined EU.

Multi-Gas Calibration

The FMA6600 Series is capable of storing primary calibration data for up to 10 gases. This feature allows the same FMA6600 Series to be calibrated for multiple gases while maintaining the rated accuracy on each.

Standard 10-Point NIST Calibration

Optional up to 9 additional 10-point calibration may be ordered at an additional charge of _____ per gas.

Conversion Factors

Conversion factors for up to 32 gases are stored in the FMA6600 and FMA 6700 Series. In addition the provision is made for a user defined conversion factor. Conversion factors may be applied to any of the ten gas calibrations via keypad or digital interface commands.

Contact Closure

Two sets of dry contact relay outputs are provided to actuate user supplied equipment. These are programmable via local keypad or digital interface such that the relays can be made to switch when a specified event occurs (e.g. when a low or high flow, pressure or temperature alarm limit is exceeded or when the totalizer reaches a specified value).

Leak Integrity

1 x 10⁻⁹ sccs of Helium maximum to the outside environment.



SPECIFICATIONS

Accuracy:

FMA6700: ±1% of FS including linearity [0 to 50°C and 0.35 to 6.8 bar (5 to 100 psia)]

FMA6600: ±1% of FS at calibration conditions [101 KPA (14.7 psia) and 21.1°C (70°F)]

Pressure Range: 0 to 6.8 bar (100 psig) (measurement)

Pressure Accuracy: ±1% of FS

Temperature Range: 0 to 50°C (measurement)

Temperature: ±1°C accuracy

Repeatability: ±0.15% of full scale

Response Time: 0.6 to 1.0 second to within ±2% of setpoint over 20% to 100% of full scale

Temp. Coefficient: 0.15% of full scale/°C or better.

Pressure Coefficient: 0.01% of full scale/psi (0.07 bar) or better

Max Gas Pressure: 6.8 bar (100 psig)

Max Burst Pressure: 13.6 bar (200 psig)

Max Pressure Drop: 8 psi (at 100 L/min flow)

Gas & Ambient Temp: 5 to 50°C (41 to 122°F)

Output Signals: Linear 0 to 5 Vdc (3000 Ω min load impedance); 0 to 10 Vdc (6000 Ω min impedance);

4 to 20 mA optional (500 Ω max loop resistance). Maximum noise 20 mV peak to peak.

Input Power: May be configured for three different options: ±15Vdc (±200 mA maximum); +12Vdc (300 mA maximum) optional; +24Vdc (250 mA maximum) optional; Circuit boards have built-in polarity reversal protection. Resettable fuses provide power input protection.

Materials in Fluid Contact: 316 stainless steel, FKM O-rings. EPDM or Perfluoroelastomer O-rings optional

Connections:

Models >= 15 LPM: Standard ¼" compression fittings

Models 20 to 50 LPM: Standard ¼" compression fittings

Models 60 to 100 LPM: Standard ⅜" compression fittings

Display: 128 x 64 graphic LCD with backlight (up to 8 lines of text)

Calibration: Standard one 10 points NIST calibration. Optional up to 9 additional calibrations may be ordered for an additional charge of _____ per gas.



CE Compliance: EN 55011 class 1, class B; EN50082-1

Environmental (per IEC 664): Installation Level II; Pollution Degree II

Approximate Shipping Weights:

Models up to 15 SLPM: 1.68 kg (3.7 lb)

Models from 20 to 100 LPM: 1.97 kg (4.34 lb)



MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)		Max Flow (N ₂)	Compression Fitting
FMA6601	FMA6701	10 cc/min SCCM	¼"
FMA6602	FMA6702	20 cc/min SCCM	¼"
FMA6603	FMA6703	50 cc/min SCCM	¼"
FMA6604	FMA6704	100 cc/min SCCM	¼"
FMA6605	FMA6705	200 cc/min SCCM	¼"
FMA6606	FMA6706	500 cc/min SCCM	¼"
FMA6607	FMA6707	1 LPM	¼"
FMA6608	FMA6708	2 LPM	¼"
FMA6609	FMA6709	5 LPM	¼"
FMA6610	FMA6710	10 LPM	¼"
FMA6611	FMA6711	15 LPM	¼"
FMA6612	FMA6712	20 LPM	¼"
FMA6613	FMA6713	30 LPM	¼"
FMA6614	FMA6714	40 LPM	¼"
FMA6615	FMA6715	50 LPM	¼"
FMA6616	FMA6716	60 LPM	⅜"
FMA6617	FMA6717	80 LPM	⅜"
FMA6618	FMA6718	100 LPM	⅜"

Options

Ordering Suffix	Description
-I	4 to 20 mA output (replaces standard 0 to 5V)
-12V	12 Vdc power
-24V	24 Vdc power
-K	Perfluoroelastomer O-rings
-B	Buna O-Rings
-E	EPR O-Rings
-VCR	VCR fittings
-RS232	RS232 communications (replaces RS485)
-O2CLEAN	Cleaned for Oxygen use

Comes complete with operator's manual, software, cable (FMA65-C) and NIST traceable certificate for Nitrogen.

Power supply sold separately.

Note: Computer must be running Windows XP in order to work with supplied software.

Note: Flow rates are stated for Nitrogen at STP conditions [21.1°C (70°F) at 1 atm].

Accessories

Model No.	Description
FMA66-PW	115 Vac to ±15 Vdc power supply
FMA66-12PW	115 Vac to 12 Vdc power supply
FMA66-24PW	115 Vac to 24 Vdc power supply
FMA66-230EU	230 Vac to ±15 Vdc power supply
FMA66-12PW-230EU	230 Vac to 12 Vdc power supply
FMA66-24PW-230EU	230 Vac to 24 Vdc power supply
FMA65-C	Replacement cable 25 pin D-conn with 1.8 m (6') wire branch to power supply
ME-1851	Reference Book: Fundamentals of Gas Dynamics

Ordering Examples: FMA6609, ¼" compression fitting, 5 LPM max, and FMA66-PW, power supply,

FMA6618, ⅜" compression fitting, 100 LPM max, and FMA66-PW, power supply,

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters