

Platinum Resistance Temperature Detector Sealed with Cement in a Cylindrical Ceramic Body

FR Series Starts at

FR Series elements are designed for applications where high vibration resistance as well as high temperature stability are vital. Typical industrial applications include analytical equipment, chemical plants, and mechanical equipment. Small tolerances on diameters allow problem-free installation in protective tubes.

Specifications

Tolerance: IEC751, Class B


Nominal Resistance: 100 Ω , 500 Ω and 1000 Ω at 0°C (32°F)

Temperature Range (Continuous Operation): -70 to 500°C (-95 to 930°F)

Temperature Coefficient: TCR = 3850 ppm/K

Leads: Platinum-clad nickel wire; 6.0 mm L (0.24")

Long-Term Stability: Max R_{10} -drift 0.1% after 1000 h at 500°C (930°F)



Measuring Current: 100 Ω max, 3 mA; 500 Ω max, 1.4 mA; 1000 Ω max, 1 mA (self-heating has to be considered)


Vibration Resistance: At least 40 g acceleration at 10 to 2000 Hz; at least 100 g acceleration with 8 ms half sine wave

Environmental Conditions: Unhoused for dry environments only

Insulation Resistance: >10 M Ω at 20°C (70°F)
>1 M Ω at 500°C (930°F)

Discount Schedule

1 to 4 units	Net
5 to 10 units	.4%
11 to 24 units	.6%
25 to 49 units	.10%
50 to 99 units	.11%
100 and up	.13%



MOST POPULAR MODEL HIGHLIGHTED!

Type Model No.	Nominal Resistance (Ω)	"D" Dimensions* mm (in)	Self Heating 0°C (K/mW)	Response Time in Seconds			
				Water V = 0.4 m/s		Air V = 1 m/s	
				50%	90%	50%	90%
1PT100FR828	1 x 100	2.8 (0.11)	0.05	0.9	2.7	12.3	39.5
1PT1000FR828	1 x 1000	2.8 (0.11)	0.05	0.9	2.7	12.3	39.5
2PT100FR828	2 x 100	2.8 (0.11)	0.16	0.9	2.7	12.3	39.5
2PT1000FR828	2 x 1000	2.8 (0.11)	0.16	0.9	2.7	12.3	39.5
1PT100FR845	1 x 100	4.5 (0.18)	0.04	1.5	4.6	24.8	78.8
1PT500FR845	1 x 500	4.5 (0.18)	0.04	1.5	4.6	24.8	78.8
1PT1000FR845	1 x 1000	4.5 (0.18)	0.04	1.5	4.6	24.8	78.8
2PT100FR845	2 x 100	4.5 (0.18)	0.08	1.5	4.6	24.8	78.8
2PT1000FR845	2 x 1000	4.5 (0.18)	0.08	1.5	4.6	24.8	78.8

The measuring point for the basic value is situated 8 mm from the end of the sensor body.

* Note: Dimensions are ± 0.3 mm.

Ordering Examples: 12 1PT100FR828 less 6% quantity discount = 2PT1000FR845, 2 x 1000 Ω , 4.5 mm Dia RTD,

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters