


OMB-DAQBOARD-3000 Series

PCI 1-MHz, 16-Bit Multifunction Boards

Starts at



- Low-Cost, 1-MHz, 16-Bit Multifunction PCI Boards
- 8 Differential or 16 Single-Ended Analog Inputs (Software Selectable per Channel)
- User-Expandable—Up to 64SE/32DE Analog Inputs Including Thermocouple Measurements
- Four 16-Bit, 1-MHz Analog Outputs with Continuous Waveform Capability
- 24 High-Speed Digital I/O Lines
- Four 32-Bit Counter Input Channels with Quadrature Encoder Capability
- Ultra Low-Latency Control Output Capability (as Low as 2 μ s Latency)
- Multiple DMA Channels
- Includes DaqView Software for Instant Setup, Real-Time Viewing, Data Logging, and Optional Frequency Domain Analysis
- Support for Visual Studio and Visual Studio.NET, Including Examples for Visual C++, Visual C#, Visual Basic, and Visual Basic.NET
- Comprehensive Drivers for DASyLab and LabVIEW
- DaqCal Software Application for Easy User Calibration

The new OMB-DAQBOARD-3000 Series comprises of high-performance PCI boards offering 16-bit/1-MHz multifunction synchronous I/O at very competitive prices. This is accomplished by incorporating a high level of integration, while focusing on features that provide valuable benefits to users.

The new OMB-DAQBOARD-3000 Series features a 16-bit/1-MHz A/D converter, 16 analog input channels (user expandable to 64), up to four 16-bit/1-MHz analog outputs, 24 high-speed digital I/O, 2 timer outputs, and four 32-bit counters. All analog I/O, digital I/O, and counter/timer I/O can operate synchronously and simultaneously, guaranteeing deterministic I/O timing among all signal types. Unique to the OMB-DAQBOARD-3000 Series is a high-speed, low-latency, highly deterministic control output mode that operates independent of the PC. In this mode both digital and analog outputs can respond to analog, digital, and counter inputs as fast as 2 μ s; at least 1000 times faster than most other boards that rely on the PC for decision making.

Other Hardware Features Include:

- Encoder measurements up to 20 MHz, including Z-channel zeroing
- Frequency and pulse-width measurements with 20.83 ns resolution

OMB-DAQBOARD-3000,
shown smaller than actual size

The OMB-DAQBOARD-3000 Series provides 1-MHz sampling, synchronous multifunction I/O, analog input expansion capability and extensive software support.

- Timing mode that can measure the time between two counter inputs to 20.83 ns resolution
- Self calibration


For end-users who would prefer the same functionality, but with a USB module, see the OMB-DAQ-3000 Series.

Software

Software support for the OMB-DAQBOARD-3000 Series includes support for Visual Studio and Visual Studio.NET, including examples for Visual C++, Visual C#, Visual Basic, and Visual Basic.NET, plus comprehensive drivers for DASyLab and LabVIEW. Also included is DaqView software for quick and easy setup and collection of data without programming, along with DaqCal software, an application for easy user calibration.

The new DaqView software that is included with the OMB-DAQBOARD-3000 Series is a comprehensive application that enables setup, data logging, and real-time data viewing without any programming skills.

The optional DaqView/Pro software adds features such as direct-to-Excel enhancements, FFT analysis, statistics, etc., for a small, additional price.



Thermocouple probes sold separately

OMB-PDQ30, shown smaller than actual size

JMQSS-125U-12,

TMQSS-125U-12,

KMQSS-125U-12,



OMB-DBK215, shown smaller than actual size. The OMB-DBK215 provides 16 BNC inputs or outputs and internal screw-terminal connections.

Signal Connections

One 68-pin connector provides access to the 16SE/8DE analog input channels, 24 digital I/O lines, 6 counter/timer channels, and up to 4 analog outputs on each OMB-DAQBOARD-3000 Series board.

An externally accessible HDMI connector is also provided on the OMB-DAQBOARD-3000 Series, enabling a simple connection for the optional OMB-OMB-PDQ30 analog channel expansion module.

In addition to standard screw-terminal options for the OMB-DAQBOARD-3000 Series, the OMB-DBK215 BNC connection module can be used to provide screw-terminal access to all I/O, plus 16 BNC connectors that can be user configured.

Analog Input

The OMB-DAQBOARD-3000 Series has a 16-bit, 1-MHz A/D coupled with 16 single-ended or 8 differential analog inputs. Seven software-programmable ranges provide inputs from ± 10 V to ± 100 mV full scale (single-ended ± 10 V range on OMB-DAQBOARD-3006). Each channel can be software-configured for a different range, as well as for single-ended or differential bipolar input. The hybrid PGIA on the OMB-DAQBOARD-3000 Series is guaranteed to settle to the specified accuracy while operating at the full 1 Msample/s rate.

Analog Channel Expansion

Adding additional analog input channels for the OMB-DAQBOARD-3000 Series is easy using the optional OMB-PDQ30 expansion module. The OMB-PDQ30 connects to the OMB-DAQBOARD-3000 Series card via an OMB-CA-266-3 cable and does not occupy a PCI slot. The OMB-PDQ30 provides an additional 48SE/24DE analog inputs, software configured on a per-channel basis. The total channel capacity with an OMB-PDQ30 attached is 64 single-ended or 32 differential inputs. The measurement speed of OMB-PDQ30 channels is the same 1 Msample/s as with on-board channels.

When configured to measure thermocouple channels, the system sample rate is 10 kHz per channel. This reduction in sample rate ensures that temperature measurements are accurate, low noise, and stable.


The OMB-DAQBOARD-3000 Series also supports up to 4 boards installed into one PC, effectively quadrupling the number of channels that can be attached to one PC.

Synchronous I/O

The OMB-DAQBOARD-3000 Series can make analog measurements and read digital and counter inputs, while synchronously generating up to 4 analog outputs as well as digital pattern outputs. Additionally, digital and counter inputs do not affect the overall A/D rate because they use no time slot in the scanning sequencer. For example, one analog input channel can be scanned at the full 1-MHz A/D rate along with digital and counter input channels. The 1-MHz A/D rate is unaffected by the additional digital and counter channels. Many other data acquisition boards provide no capability to scan digital/counter channels along with analog channels, in which case digital and counter channels must be read asynchronously, which leads to a non-deterministic collection of data.



OMB-CA-266-3, OMB-DAQBOARD-3000 to OMB-PDQ30 cable



The OMB-TB-100, termination board with screw terminals, provides access to all OMB-DAQBOARD-3000 Series I/O. The OMB-TB-100 can be panel mounted or 19" rack mounted using optional OMB-RACK3 mounting kit.

Input Scanning


The OMB-DAQBOARD-3000 has several scanning modes to address a wide variety of applications. A 512 location scan buffer can be loaded by the user with any combination of analog input channels. All analog input channels in the scan buffer are measured sequentially at 1 μ s per channel. The user can also specify that the sequence repeat immediately, or repeat after a programmable delay from 0 to 19 hours, with 20.83 ns resolution. For example, in the fastest mode, with a 0 delay, a single analog channel can be scanned continuously at 1 Msamples/s; two analog channels can be scanned at 500 Ksamples/s each; 16 analog input channels can be scanned at 62.5 Ksamples/s.

OMB-DAQBOARD-3000 digital inputs and counter inputs can be read in several modes. First, via software the digital inputs or counter inputs can be read asynchronously at any time before, during, or after an analog input scan sequence. This mode is not deterministic as to exactly when the digital or counter input was read relative to an analog input channel.

In either of the two synchronous modes, the digital inputs and/or counter inputs are read with deterministic time correlation to the analog inputs. In the once-per-scan mode, all of the enabled digital inputs and counter inputs are read

during the first analog measurement of an analog input scan sequence. The advantage of this mode is that the digital and counter inputs do not occupy an analog input time slot and therefore do not reduce the available bandwidth for making analog input measurements. For example, assume all 24 bits of digital input are enabled, all four 32-bit counters are enabled, and eight channels of analog inputs are in the scan sequence at the full 1 μ s/channel rate. At the beginning of each analog input scan sequence, which would be 8 μ s in total duration, all digital inputs and counter inputs will be measured and sent to the PC during the first μ s of the analog scan sequence.

In the other synchronous mode, digital inputs are scanned every time an analog input channel is scanned. For example, if eight analog inputs are scanned at 1 μ s per channel continuously, and 24 bits of digital inputs are enabled, then the 24 bits of digital inputs will be scanned at 24 bits per 1 μ s. If counters are enabled in this mode, they will be scanned at once per scan, in the same manner as in the prior example.




OMB-DAQBOARD-3000, attached to an OMB-PDQ30 expansion module, via an OMB-CA-266-3 cable, all shown smaller than actual size


Output Timing

The digital and analog outputs on the OMB-DAQBOARD-3000 can be updated asynchronously or synchronously in several modes. In the asynchronous mode, digital and analog outputs can be updated at any time before, during, or after an analog input sequence. The maximum update rate in this mode is non-deterministic and is entirely dependent on the PC processor speed, the operating system, and the programming environment.

In the synchronous output modes, the outputs can be updated directly from memory in the PC, or as the direct result of an input from either an analog channel, digital channel, or counter channel. When updated from memory in the PC (via DMA), the rate by which the output can be specified is 20.83 ns intervals, and all outputs can be updated synchronously at a maximum rate of 1 μ s. For example, all four 16-bit analog outputs can be generating different waveforms from PC memory with a 1 μ s per channel update rate, while up to 16 bits of digital pattern could be generated from PC memory concurrently at the 1 μ s per 16-bit update rate. Outputs can also be specified to update concurrently with inputs, so there is an exact timing correlation between inputs and outputs.

The other synchronous method of output control is where an output, either digital or analog, is associated with any input— analog, digital, or counter.





OMB-DAQBOARD-3000, attached to an OMB-DBK215 BNC and screw-terminal module,

The state or level of the output is determined by the level or state of an associated input. For example, a digital output could be programmed to be a logic 1 when an analog input exceeds a certain value, or when a frequency input exceeds a certain rate. In addition, hysteresis can be programmed for each limit to ensure the output is stable near the transition point. Up to 8 digital outputs and 4 analog outputs can be programmed to respond to any analog, digital, or counter input. When analog or digital outputs are used in this mode, the user can specify two output values, determined by whether the input is above or below the limit.

The slowest rate at which an analog output can respond to an input is 4 μ s plus the time period of a scan sequence. For example, if 4 channels of analog input are scanned continuously at 4 μ s per scan, then the maximum latency between an analog input satisfying a limit, and the output responding, is 4 + 4 or 8 μ s max. The worst-case response time can also be improved in several ways. For example, if a digital output is correlated to a digital input, then the worst-case latency can be reduced to 2 μ s total if all digital inputs are scanned at the 1 μ s rate without a delay period at the end of each scan.

In addition, an output status channel can be specified in the input scan sequence buffer so that users can correlate output state changes to their respective input channels within their data buffers and files. Adding the status channel takes no additional scan time and has no effect on the overall acquisition rate. The status channel can also be read asynchronously at any time during an acquisition for monitoring of the control outputs.

The advantage of this mode is that the response time can be in the range of 2 to 20 μ s, vs. 1000 or more microseconds when using other suppliers' boards.

Triggering

The OMB-DAQBOARD-3000 Series supports a full complement of trigger modes to accommodate any measurement situation.

Hardware Analog Triggering. The OMB-DAQBOARD-3000 Series uses true analog triggering, whereby the trigger level programmed by the user sets an analog DAC, which is then compared in hardware to the analog input level on the selected channel. The result is analog trigger latency that is guaranteed to be less than 1 μ s, significantly shorter than most data acquisition boards. Any analog channel can be selected as the trigger channel, including OMB-PDQ30 expansion channels. The user can program both the trigger level, as well as the edge (rising or falling) and hysteresis.

Digital Triggering. A separate digital trigger input line is provided, allowing TTL-level triggering with latencies guaranteed to be less than 1 μ s. Both the logic levels (1 or 0), as well as the edge (rising or falling), can be programmed for the discrete digital trigger input.

Pattern Triggering. The user can specify a 16-bit digital pattern to trigger an acquisition, including the ability to mask or ignore specific bits.

Software-Based Channel Level Triggering. This mode differs from the modes described previously because the readings analog, digital, or counter are interrogated by the PC in order to detect the trigger event. Triggering can also be programmed to occur when one of the counters reaches, exceeds, or is within a programmed window. Any of the built-in counter/totalizer channels can be programmed as a trigger source. Triggers can be detected on scanned digital input channel patterns as well.

Normally, software-based triggering results in long latencies, from the time a trigger condition is detected until the actual capturing of data commences. However, the OMB-DAQBOARD-3000 Series circumvents this undesirable situation by use of pre-trigger data. Specifically, when software-based triggering is employed, and the PC detects that a trigger condition has occurred (which may be thousands of readings later than the actual occurrence of the signal), the DaqBoard driver automatically looks to the location in memory where the actual trigger-causing measurement occurred. The acquired data that is presented to the user actually begins at the point where the trigger-causing measurement occurs. The maximum latency in this mode is equal to one scan period.

Stop Trigger. Any of the software trigger modes described previously, including scan count, can also be used to stop an acquisition. Thus an acquisition can be programmed to begin on one event, such as a voltage level, and stop on another event, such as a digital pattern.

OMB-DAQBOARD-3000 Series Selection Chart and OMB-PDQ30 Expansion Capabilities

Model Number	Analog Inputs	Input Ranges	Digital I/O	Analog Outputs	Counters/ Timers
OMB-DAQBOARD-3006	16 SE	1	24	0	4/2
OMB-DAQBOARD-3005	16SE/8DE	7	24	0	4/2
OMB-DAQBOARD-3000	16SE/8DE	7	24	2	4/2
OMB-DAQBOARD-3001	16SE/8DE	7	24	4	4/2
OMB-DAQBOARD-3005 & OMB-PDQ30	64SE/32DE	7	24	0	4/2
OMB-DAQBOARD-3000 & OMB-PDQ30	64SE/32DE	7	24	2	4/2
OMB-DAQBOARD-3001 & OMB-PDQ30	64SE/32DE	7	24	4	4/2

Pre- and Post-Triggering Modes.

Six modes of pre- and post-triggering are supported, providing a wide variety of options to accommodate any measurement requirement. When using pre-trigger, the user must use software-based triggering to initiate an acquisition.

No Pre-Trigger, Post-Trigger Stop Event. This mode acquires data upon receipt of the trigger and stops acquiring upon receipt of the stop-trigger event.

Fixed Pre-Trigger with Post-Trigger Stop Event. In this mode, the user specifies the number of pre-trigger readings to be acquired, after which acquisition continues until a stop-trigger event occurs.

No Pre-Trigger, Infinite Post-Trigger. No pre-trigger data is acquired in this mode. Instead, data is acquired beginning with the trigger event and is terminated when the operator issues a command to halt the acquisition.

Fixed Pre-Trigger with Infinite Post-Trigger. The user specifies the amount of pre-trigger data to acquire, after which the system continues to acquire data until the program issues a command to halt acquisition.


Variable Pre-Trigger with Post Trigger Stop Event (Driver Support Only). Unlike the previous pre-trigger modes, this mode does not have to satisfy the pre-trigger number of readings before recognizing the trigger event. Thus the number of pre-trigger readings acquired is variable and dependent on the time of the trigger event relative to the start.

Voltage Range*	Accuracy ± (% of Reading + % Range) 23°C, ±10°C, 1 Year	Temperature Coefficient ± (ppm of Reading + ppm Range) /°C 0 to 13°C and , 33 to 60°C	Noise* (cts RMS)
-10 V to 10 V	0.031% + 0.008%	14 + 8	1.5
-5 V to 5 V	0.031% + 0.009%	14 + 9	2.0
-2 V to 2 V	0.031% + 0.010%	14 + 10	1.6
-1 V to 1 V	0.031% + 0.012%	14 + 12	2.5
-500 mV to 500 mV	0.031% + 0.018%	14 + 18	4.0
-200 mV to 200 mV	0.036% + 0.012%	14 + 12	5.0
-100 mV to 100 mV	0.042% + 0.018%	14 + 18	9.0

* Specifications assume differential input single channel scan, 1-MHz scan rate, unfiltered, CMV=0.0V, 30 minute warm-up,

** Noise reflects 10,000 samples at 1-MHz, typical, differential short, OMB-CA-G56

OMB-DAQBOARD-3000 Series Block Diagram



In this mode, data continues to be acquired until the stop trigger event is detected.

Variable Pre-Trigger with Infinite Post Trigger (Driver Support Only). This mode is similar to the mode described above, except that the acquisition is terminated upon receipt of a command from the program to halt the acquisition.

Calibration

Every range on the OMB-DAQBOARD-3000 is calibrated from the factory using a digital NIST-traceable calibration method. This method works by storing a correction factor for each range on the unit at the time of calibration. Users can adjust the calibration of the board while in their

system, without destroying the factory calibration supplied with the board. This is made possible by having 3 distinct calibration tables in the OMB-DAQBOARD-3000 Series on-board EPROM, one that contains the factory cal and two that are available for user calibration. The user can select any of the 3 cal tables provided: factory, user- or self-cal tables by API call or within the software provided.

Included with each OMB-DAQBOARD-3000 is DaqCal software, an easy-to-operate package that allows users to calibrate their boards. Two calibration modes are supported in DaqCal. Self-cal, a user cal mode for analog inputs, can be performed automatically in minutes with

included software and without the use of external hardware or instruments. Self-cal derives its traceability through an on-board reference that has a stability of 0.005% per year. The second mode, user-cal, is for users who require traceability to international standards such as NIST. A 6½ digital multimeter is required and user-calibration software is included with step-by-step instructions for full calibration. A 2-year calibration period is recommended for the OMB-DAQBOARD-3000 Series.

Analog Output (OMB-DAQBOARD-3000 and OMB-DAQBOARD-3001 only)

Two or four 16-bit, 1-MHz analog output channels are built into the OMB-DAQBOARD-3000 Series with an output range of -10 V to 10 V. Through the use of bus mastering DMA, each D/A output can continuously output a waveform at up to 1 MHz, which can be read from PC RAM or a file on the hard disk. In addition, a program can asynchronously output a value to any of the D/As for non-waveform applications, assuming the D/A is not already being used in the waveform output mode. Lastly, each of the analog outputs can be used in a control mode, where their output level is dependent on whether an associated analog, digital, or counter input is above or below a user-specified limit condition.


When used to generate waveforms, the D/As can be clocked in several different modes. Each D/A can be separately selected to be clocked from one of the sources described below.

Asynchronous Internal Clock.

The on-board programmable clock can generate updates ranging from once every 19 hours to 1 MHz, independent of any acquisition rate.

Synchronous Internal Clock. The rate of analog output update can be synchronized to the acquisition rate derived from 1 MHz to once every 19 hours.

Asynchronous External Clock. A user-supplied external input clock can be used to pace the D/A, entirely independent of analog inputs.



OMB-DAQBOARD-3000,
shown smaller than actual size

The OMB-DAQBOARD-3000 Series provides 1-MHz sampling, synchronous multifunction I/O, analog input expansion capability and extensive software support.

Synchronous External Clock.

A user-supplied external input clock can pace both the D/A and the analog input.

Digital I/O

Twenty-four TTL-level digital I/O lines are included in the OMB-DAQBOARD-3000 Series. Digital I/O can be programmed in 8-bit groups as either inputs or outputs and can be scanned in several modes (see Input Scanning). Ports programmed as inputs can be part of the scan group and scanned along with analog input channels, or they can be asynchronously accessed via the PC at any time, including when a scanned acquisition is occurring. Two synchronous modes are supported when scanned along with analog inputs. In the first mode, the digital inputs are scanned at the start of each scan sequence, which means the rate at which they are scanned is dependent on the number of analog input channels and the delay period. For example, if 8 analog inputs are enabled with 0 delay period, then the digital inputs in this mode would be scanned at once per 8 μs, which is 125 kHz.

In the other synchronous mode, the enabled digital inputs are scanned synchronously with every analog input channel. So in the example above, the digital inputs would be scanned at once per μs, or 1 MHz. If no analog inputs are being scanned, the digital inputs can be scanned at up to 12 Msamples/s.



OMB-CA-G56,
68-conductor shielded cable from OMB-DAQBOARD-3000 Series to OMB-TB-100 or OMB-DBK215.

Digital Outputs and Pattern Generation

Digital outputs can be updated asynchronously at any time before, during, or after an acquisition. Two of the 8-bit ports can also be used to generate a 16-bit digital pattern at up to 12 MHz. The OMB-DAQBOARD-3000 Series supports digital pattern generation via bus mastering DMA. In the same manner as analog output, the digital pattern can be read from PC RAM or from a file on the hard disk. Digital pattern generation is clocked in the same four modes as previously described for analog output.

The ultra low-latency digital output mode allows a digital output to be updated based on the level of an analog, digital, or counter input. In this mode, the user associates a digital output bit with a specific input and specifies the level of the input where the digital output changes state.

The response time in this mode depends on the number of input channels being scanned and can typically be in the range of 2 to 20 μ s.

Counter Inputs

Four 32-bit counters are built into the OMB-DAQBOARD-3000 Series. Each of the four counters will accept frequency inputs of up to 20 MHz, and each counter channel can be configured in a variety of modes, including counter, period, pulse width, time between edges, or multi-axis quadrature encoder. The counters can concurrently monitor time periods, frequencies, pulses, and other event-driven incremental occurrences from encoders, pulse generators, limit switches, proximity switches, and magnetic pick-ups.

As with all other inputs to the OMB-DAQBOARD-3000 Series, the counter inputs can be read asynchronously under program control, or synchronously as part of an analog and digital scan group based either on an internal programmable timer or an external clock source.

The OMB-DAQBOARD-3000 supports quadrature encoders with up to 2 billion pulses per revolution; 20 MHz input frequencies; and x1, x2, x4 count modes. With only A phase and B phase signals, 2 channels are supported. With A phase, B phase, and Z index signals, 1 channel is supported. Each input can be debounced from 500 ns to 25.5 ms (total of 16 selections) to eliminate extraneous noise or switch-induced transients. Encoder input signals must be within -15 V to 15 V and the switching threshold is TTL (1.3 V). Power is available for encoders, 5 V at up to 500 mA.

Timer Outputs

Two 16-bit timer outputs are built into the OMB-DAQBOARD-3000, each capable of generating different square waves with a programmable frequency range from 16 Hz to 1 MHz.

Multiple DaqBoards per PC

All of the features described for the OMB-DAQBOARD-3000 can be replicated with up to four OMB-DAQBOARD-3000s installed

in the same PC. The serial number on each OMB-DAQBOARD-3000 is used to differentiate one from another, and a user-selected name can be assigned to each board for easy program documentation. When multiple boards are installed, all boards can be operated synchronously by designating one board as the master. All of the other boards are then slaves, and are synchronized to the master via the pacer clock, which is externally routed to the designated slave boards.

Specifications

General Power Consumption

(per board): 3 W

Operating Temperature:

0 to 60°C (32 to 140°F)

PCI Bus: PCI r2.2 compliant,

universal 3.3 V/5 V signaling support, compatible with PCI-X

Storage Temperature:

-40 to 80°C (-40 to 176°F)

Relative Humidity:

0 to 95% non-condensing

Vibration:

MIL STD 810E cat 1 and 10

Signal I/O Connector: 68-pin standard "SCSI Type III" female connector

Dimensions:

165 W x 15 x 108 mm H
(6.5 x 0.6 x 4.2")

Weight: 160 g (0.35 lb)

ANALOG INPUTS

Channels: 16 single-ended (SE) or 8 differential (DE), programmable on a per-channel basis as single-ended or differential (except for OMB-DAQBOARD-2006, which is limited to 16 SE analog inputs with a fixed range of 10 V)

Expansion:

An additional 48 analog inputs per board via optional OMB-PDQ30 module; expansion channels have identical features as the main board channels (except for OMB-DAQBOARD-2006, which is limited to 16 SE analog inputs with a fixed range of 10 V)

Expansion Connector:

HDMI connector (except for OMB-DAQBOARD-2006, which is limited to 16 SE analog inputs with a fixed range of 10 V)

Over-Voltage Protection:

\pm 30 V without damage

Ranges: Software- or sequencer-selectable on a per channel basis, \pm 10 V, \pm 5 V, \pm 2 V, \pm 1 V, \pm 0.5 V, \pm 0.2 V, \pm 0.1 V (except for OMB-DAQBOARD-2006, which is limited to 16 SE analog inputs with a fixed range of 10V)


Input Impedance:


10 M Ω single-ended; 20 M Ω differential

Total Harmonic Distortion:

-80 dB type for \pm 10 V range, 1 kHz fundamental

DAQVIEW software included with the OMB-DAQBOARD-3000 Series





OMB-DAQBOARD-3000, attached to an OMB-TB-100 terminal board,

Signal to Noise and Distortion:

72 dB type for ± 10 V range, 1 kHz fundamental

Bias Current:

40 pA typical (0 to 35°C)

Crosstalk: -75 dB typical DC to 60 Hz; -65 dB typical @ 10 kHz

Common Mode Rejection:

-70 dB typical DC to 1 kHz

A/D Specifications

Type: Successive approximation

Resolution: 16 bit

Maximum Sample Rate: 1 MHz

Non-Linearity (Integral):

± 2 LSB maximum

Non-Linearity (Differential):

± 1 LSB maximum

Input Sequencer

Analog, digital, and frequency inputs can be scanned synchronously, based on either an internal programmable timer or an external clock source. Analog and digital outputs can be synchronized to either of these clocks.

Scan Clock Sources: 2

The maximum scan clock rate is the inverse of the minimum scan period. The minimum scan period is equal to 1 μ s times the number of analog channels. If a scan contains only digital channels, then the minimum scan period is 83 ns times the number of digital channels.

1. Internal, programmable analog channels from 1 μ s to 19 hours in 20.83 ns steps; digital channels and counters from 83.33 ns to 19 hours in 20.83 ns steps
2. External, TTL level input analog channels down to 1 μ s min; digital channels and counters down to 83 ns min

Programmable Parameters per Scan: Channel (random order), gain
Depth: 512 locations
On-Board Channel-to-Channel Scan Rate:

Analog: 1 MHz maximum
Digital: 12 MHz if no analog channels are enabled, 1 MHz with analog channels enabled

External Acquisition Scan Clock

Input Maximum Rate: 1.0 MHz
Clock Signal Range: Logical zero 0 V to 0.8 V; logical one 2.4 V to 5.0 V
Minimum Pulse Width: 50 ns high, 50 ns low

TRIGGERING

Trigger Sources: 6, individually selectable for starting and stopping an acquisition. Stop acquisition can occur on a different channel than start acquisition; stop acquisition can be triggered via modes 2, 4, 5, or 6 described below.

1. SINGLE-CHANNEL ANALOG HARDWARE TRIGGER

Any analog input channel can be software programmed as the analog trigger channel, including any of the analog expansion channel

Input Signal Range:

-10 to 10 V max

Trigger Level:

Programmable (12-bit resolution)

Hysteresis:

Programmable (12-bit resolution)

Latency:


350 ns typ, 1.3 μ s max

Accuracy:

$\pm 0.5\%$ of reading, ± 2 mV offset

Noise: 2 mV RMS

The OMB-TB-100, termination board with screw terminals, provides access to all OMB-DAQBOARD-3000 Series I/O. The OMB-TB-100 can be panel mounted or 19" rack mounted using optional OMB-RACK3 mounting kit.



2. SINGLE-CHANNEL ANALOG SOFTWARE TRIGGER

Any analog input channel, including any of the analog expansion channels, can be selected as the software trigger channel. If the trigger channel involves a calculation, such as temperature, then the driver automatically compensates for the delay required to obtain the reading, resulting in a maximum latency of one scan period.
Input Signal Range: Anywhere within range of the selected trigger channel

Trigger Level: Programmable (16-bit resolution), including "window triggering"

Latency: One scan period max

3. SINGLE-CHANNEL DIGITAL TRIGGER

A separate digital input is provided for digital triggering.

Input Signal Range:

-15 V to 15 V

Trigger Level: TTL

Minimum Pulse Width:

50 ns high, 50 ns low

Latency: 100 ns typ, 1.1 μ s max

4. DIGITAL PATTERN TRIGGERING

8- or 16-bit pattern triggering on any of the digital input ports. Programmable for trigger on equal, above, below or within/outside of a window. Individual bits can be masked for "don't care" condition.

Latency: One scan period max

5. COUNTER/TOTALIZER TRIGGERING

Counter/totalizer inputs can trigger an acquisition. User can select to trigger on a frequency or on total counts that are equal, above, below, or within/outside of a window.

Latency: One scan period, max

6. SOFTWARE TRIGGERING

Trigger can be initiated under program control.

ANALOG OUTPUTS (OMB-DAQBOARD-3000 and OMB-DAQBOARD-3001 only)

Analog output channels are updated synchronously relative to scanned inputs and clocked from either an internal on-board clock or an external clock source. Analog outputs can also be updated asynchronously, independent of any other scanning in the system. Bus mastering DMA provides CPU and system-independent data transfers, ensuring accurate outputs that are irrespective of other system activities. Streaming from disk or memory is supported, allowing continuous, nearly infinite length, waveform outputs (limited only by available PC system resources).
Channels: 2 (OMB-DAQBOARD-3000); 4 (OMB-DAQBOARD-3001)

Resolution: 16-bits

Data Buffer: PC-based memory

Output Voltage Range: ± 10 V

Output Current: ± 10 mA

Offset Error: ± 0.0045 V max

Digital Feedthrough:

<10 mV when updated

DAC Analog Glitch:

<12 mV typical at major carry

Gain Error: $\pm 0.01\%$

Update Rate: 1 MHz max, 19 hours min (no minimum with external clock), resolution 20.83 ns
Settling Time: 2 μ s max to 1 LSB for full-scale step

Clock Sources: 4, programmable

1. On-board D/A clock, independent of scanning input clock
2. Onboard scanning input clock
3. External D/A input clock, independent of external scanning input clock
4. External scanning input clock

DIGITAL I/O

Channels: 24

Ports: 3 x 8-bit, each port is programmable as input or output
Input Scanning Modes: 2 programmable

1. Asynchronous, under program control at any time relative to input scanning
2. Synchronous with input scanning



OMB-CA-G55, 68-conductor low-cost cable.

Input Characteristics: 10 K Ω pull up to 5V, 20 pF to common

Input Protection:

± 15 kV ESD clamp diodes

Input Levels:

Low: 0 to 0.8 V

High: 2.0 V to 5.0 V

Output Levels:

Low: <0.8 V

High: >2.0 V

Output Characteristics:

Output 12 mA per pin, 200 mA total continuous

Sampling/Update Rate:

12 MHz max

PATTERN GENERATION OUTPUT

Two of the 8-bit ports can be configured for 16-bit pattern generation. The pattern can also be updated synchronously with an acquisition at up to 12 MHz.

Counter:

Each of the 4 high-speed, 32-bit counter channels can be configured for counter, period, pulse width, time between edges, or multi-axis quadrature encoder modes. Counter inputs can be scanned synchronously along with analog and digital scanned inputs, based on an internal programmable timer or an external clock source.

Channels: 4 x 32 bit

Input Frequency: 20 MHz max

Input Signal Range: -15 V to 15 V

Input Characteristics: 10 K Ω pull-up, ± 15 kV ESD protection

Trigger Level: TTL

Minimum Pulse Width:

25 ns high, 25 ns low

Debounce Times: 16 selections from 500 ns to 25.5 ms; positive or negative edge sensitive; glitch detect mode or debounce mode

Time Base Accuracy:

30 ppm (0 to 50°C)

Five Programmable Modes:

Counter, period, pulsewidth, timing, encoder

Counter Mode Options:

Totalize, clear on read, rollover, stop at all Fs, 16- or 32-bit, any other channel can gate or decrement the counter

Period Mode Options:

Measure x1, 10, 100 or 1000 periods; 16- or 32-bit; 4 different time bases to choose from: 20.83 ns, 208.3 ns, 2.083 μ s, 20.83 μ s, any other channel can gate the period measurement

Pulsewidth Mode Options:

16- or 32-bit values; 4 different time bases to choose from: 20.83 ns, 208.3 ns, 2.083 μ s, 20.83 μ s, any other channel can gate the pulsewidth measurement

Timing Mode Options:

16- or 32-bit values; 4 different time bases to choose from: 20.83 ns, 208.3 ns, 2.083 μ s, 20.83 μ s

Encoder Mode Options:

x1, 2, 4 options; 16- or 32-bit values; Z-channel clearing of counter; any other channel can gate the counter

Power Available for Encoders:

5 V @ 500 mA max

Multi-Axis Quadrature

Encoder Inputs:

- 1 channel with A (phase) B (phase) and Z (index)
- 2 channel with A (phase) and B (phase)
- x1, x2 and x4 count modes
- Single-ended TTL

Frequency/Pulse Generators

Channels: 2 x 16-bit

Output Waveform: Square wave

Output Rate: 1 MHz base rate divided by 1 to 65535 (programmable)

High-Level Output Voltage:


2.0 V min @ -1.0 mA; 2.9 V min @ -400 μ A

Low-Level Output Voltage:

0.4 V max @ 400 μ A

OMB-PDQ30 EXPANSION MODULE

See the OMB-PDQ30 data sheet for complete specifications



OMB-CA-G56,
68-conductor shielded cable from
OMB-DAQBOARD-3000 Series to
OMB-TB-1000 or OMB-DBK215.

The OMB-DAQBOARD-3000 Series provides 1-MHz sampling, synchronous multifunction I/O, analog input expansion capability and extensive software support.

ALL MODELS AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model No.		Description
OMB-DAQBOARD-3006		16-bit, 1-MHz PCI data acquisition board with 16 analog inputs with a single-ended 10 V range (not expandable with OMB-PDQ30), 24 digital I/O, four counters, and two timers; includes DaqView; support for Visual Studio and Visual Studio.NET, including examples for Visual C++, Visual C#, Visual Basic and Visual Basic.NET; drivers for DASyLab, and LabVIEW; and DaqCal software application for easy user-calibration
OMB-DAQBOARD-3005		16-bit, 1-MHz PCI data acquisition board with 8DE/16SE analog inputs, 7 input ranges from 100 mV to 10 V full-scale, 24 digital I/O, four counters and two timers; includes DaqView; support for Visual Studio and Visual Studio .NET, including examples for Visual C++, Visual C#, Visual Basic and Visual Basic .NET; drivers for DASyLab, and LabVIEW; and DaqCal software application for easy user-calibration
OMB-DAQBOARD-3000		Same as OMB-DAQBOARD-3005 but with two 16-bit, 1-MHz analog outputs
OMB-DAQBOARD-3001		Same as OMB-DAQBOARD-3005 but with four 16-bit, 1-MHz analog outputs
OMB-PDQ30		Analog input expansion module, adds 48SE/24DE channels to OMB-DAQBOARD-3000 Series; connects via an OMB-CA-266-3 cable

Accessories

Model No.		Description
OMB-TB-100		Termination board with screw terminals for access to OMB-DAQBOARD-3000 Series I/O; connects via an OMB-CA-G55, OMB-CA-G56 or OMB-CA-G56-6 cable
OMB-RACK3		Rack-mount kit for OMB-TB-100
OMB-DBK215		BNC termination module with 16 BNC connectors and internal screw-terminal connections; connects via an OMB-CA-G55, OMB-CA-G56 or OMB-CA-G56-6 cable
OMB-CA-G55		68-conductor ribbon expansion cable from OMB-DAQBOARD-3000 Series boards to OMB-TB-100 or OMB-DBK215, 0.9 m (3 ft)
OMB-CA-G56		68-conductor shielded cable from OMB-DAQBOARD-3000 Series boards to OMB-TB-100 or OMB-DBK215, 0.9 m (3 ft)
OMB-CA-G56-6		68-conductor shielded cable from OMB-DAQBOARD-3000 Series boards to OMB-TB-100 or OMB-DBK215, 1.8 m (6 ft)
OMB-CA-266-3		HDMI cable, connects OMB-PDQ30 to OMB-DAQBOARD-3000 Series, 0.9 m (3 ft)

Each OMB-DAQBOARD-3000 Series board is supplied with DaqView software, software drivers and complete operator's manual on CD ROM.
Ordering Example: OMB-DAQBOARD-3005, 16-bit, 1-MHz PCI data acquisition board with 8DE/16SE analog inputs, 7 input ranges from 100 mV to 10 V full-scale, 24 digital I/O, four counters and two timers, OMB-TB-100 termination board, OMB-CA-G56 shielded cable and OMEGACARE™ 1-year extended warranty for OMB-DAQBOARD-3005 (adds 1 year to standard 1-year warranty),

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters