

PRODUCT-DETAILS

F202 A-100/0.03 110V

F202 A-100/0.03 110V Residual Current Circuit Breaker 2P A type 30 mA



General Information

Extended Product Type	F202 A-100/0.03 110V
Product ID	2CSF202199R1100
EAN	8012542342939
Catalog Description	F202 A-100/0.03 110V Residual Current Circuit Breaker 2P A type 30 mA
Long Description	The RCCBs F200 series assures protection against the effects of sinusoidal alternating and direct pulsating earth fault currents, protection, against indirect contacts and additional protection against direct (with sensitivity = 30 mA) contacts. Applications: residential, commercial, industrial. This particular series has the minimum operating voltage of test bottom of 110V and it is suitable for application at 230V.

Circular Value

Circular Design Principles Recyclability Rate	Design for Closing Resource Loops - Standard EN45555 - 52,5 %
Sustainable Material Content	0 %
End of Life Instructions	9AKK108468A4361

Eco Transparency

Environmental Product Declaration - EPD	9AKK108467A3700
--	-----------------

Technical

Standards	IEC 61008 UL 1053
Type of Residual Current	A type
Rated Voltage (U_r)	230 V
Rated Operational Voltage	230 V
Rated Insulation Voltage (U_i)	500 V
Test Voltage (U_t)	110 V
Rated Impulse Withstand Voltage (U_{imp})	4 kV
Input Voltage Type	AC
Rated Current (I_n)	100 A
Rated Residual Current	30 mA
Rated Conditional Short-Circuit Current (I_{nc})	10 kA
Rated Service Short-Circuit Breaking Capacity (I_{cs})	1 kA
Leakage Current Type	A
Rated Frequency (f)	50 ... 60 Hz
Power Loss	at Rated Operating Conditions per Pole 6.5 W
Power Supply Connection	Arbitrary
Electrical Endurance	10000 cycle
Number of Poles	2
Operating Characteristic	Instantaneous
Mounting Type	DIN-Rail
Options Provided	None, Suitable for 110V applications
Accessories Available	Yes
Connecting Capacity	Busbar 10 mm ² Rigid 35 ... 35 mm ² Flexible 35 ... 35 mm ²
Rated Cross-Section	4 - Multi-Wired 0...35 mm ² 1 - Solid-Core 35...35 mm ²

Environmental

Ambient Temperature	-25...55 °C
Ambient Air Temperature	Operation -25...55 °C
Degree of Protection	IP2X
Pollution Degree	2
Resistance to Vibrations acc. to IEC 60068-2-6	0.1 mm or 1 g - 20 cycles at 5...150...5 Hz
Resistance to Shock acc. to IEC 60068-2-27	25g 2 shocks 13 ms
RoHS Status	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
RoHS Information	9AKK106713A5602
REACH Declaration	9AKK108467A9482
Environmental Information	Refer to RoHS
Conflict Minerals Reporting Template (CMRT)	9AKK108468A3363

Technical UL/CSA

Maximum Operating Voltage UL/CSA	277 V AC
Short-Circuit Current Rating (SCCR)	30 mA

Dimensions

Width in Number of Modular Spacings	2
Product Net Width	0.035 m
Product Net Height	0.085 m
Product Net Depth / Length	0.069 m
Product Net Weight	0.200 kg
Built-In Depth (t ₂)	69 mm

Ordering

Minimum Order Quantity	1 piece
Package Level 1 Units	box 1 piece
Package Level 1 Gross Weight	0.235 kg
Customs Tariff Number	85363030
Country of Origin	Italy (IT)

Certificates and Declarations

Declaration of Conformity - CE	9AKK106713A5602
--------------------------------	-----------------

Popular Downloads

Data Sheet, Technical Information	9AKK107991A8329
Instructions and Manuals	9AKK107991A6127
EPLAN Macro	9AKK106930A1238

Classifications

ETIM 8	EC000003 - Residual current circuit breaker (RCCB)
ETIM 9	EC000003 - Residual current circuit breaker (RCCB)
EPLAN Catalog Tree	Electrical engineering / Protection devices / Ground fault current circuit breaker
EPLAN Function Definition	Ground fault current circuit-breaker / Ground fault current circuit breakers, 4 connection points / Ground fault current circuit breaker, two-pole 1/2 2/1 3/4 4/3
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Consumer
CN8	85363030
UNSPSC	39121601
eClass	V11.0 : 27142201
IDEA Granular Category Code (IGCC)	4875 >> Residual current circuit breaker (RCCB)

Object Classification Code

F

Accessories

Identifier	Description	Type	Quantity	Unit Of Measure
2CDS200912R0001	S2C-H6R Auxiliary Contact	S2C-H6R	2	piece
2CDS200922R0001	S2C-S/H6R Signal / Auxiliary Contact	S2C-S/H6R	2	piece
2CDS200946R0001	S2C-H6-11R Auxiliary Contact	S2C-H6-11R	1	piece
2CDS200946R0003	S2C-H6-02R Auxiliary Contact	S2C-H6-02R	1	piece
2CDS200946R0002	S2C-H6-20R Auxiliary Contact	S2C-H6-20R	1	piece
2CSS200933R0011	F2C-A1 Shunt trip	F2C-A1	1	piece
2CSS200933R0012	F2C-A2 Shunt trip	F2C-A2	1	piece
2CSS200911R0005	S2C-UA 230 AC Undervoltage release	S2C-UA 230 AC	1	piece
2CSS200911R0007	S2C-UA 24 DC Undervoltage release	S2C-UA 24 DC	1	piece
2CSS200911R0002	S2C-UA 24 AC Undervoltage release	S2C-UA 24 AC	1	piece
2CSS200911R0008	S2C-UA 48 DC Undervoltage release	S2C-UA 48 DC	1	piece
2CSS200911R0004	S2C-UA 110 AC Undervoltage release	S2C-UA 110 AC	1	piece
2CSS200911R0006	S2C-UA 400 AC Undervoltage release	S2C-UA 400 AC	1	piece
2CSS200911R0001	S2C-UA 12 DC Undervoltage release	S2C-UA 12 DC	1	piece
2CSS200911R0010	S2C-UA 230 DC Undervoltage release	S2C-UA 230 DC	1	piece
2CSS200911R0009	S2C-UA 110 DC Undervoltage release	S2C-UA 110 DC	1	piece
2CSS200911R0003	S2C-UA 48 AC Undervoltage release	S2C-UA 48 AC	1	piece
2CSS200910R0005	S2C-OVP1 Overvoltage release	S2C-OVP1	1	piece
2CSS200993R0005	S2C-OVP2 Overvoltage release	S2C-OVP2	1	piece
2CSF200997R0013	F2C-CM Motor operating device	F2C-CM	1	piece
2CSF200996R0013	F2C-ARI Auto-reclosing unit	F2C-ARI	1	piece

Categories

Low Voltage Products and Systems → Modular DIN Rail Products → Residual Current Devices RCDs → Residual Current Devices RCDs

