



Click [here](#) for the 3D model.

Dimensions

L	18mm +/-0.5mm
H	16mm +0.1/-0.5mm
T	10mm +0.2/-0.5mm
S	15mm +/-0.4mm
LL	4mm +2mm
F	0.8mm +/-0.05mm

Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	750

General Information

Series	R71
Dielectric	Metallized Polypropylene
Style	Radial
Features	PFC and Pulse
RoHS	Yes
Lead	Cut
AEC-Q200	No
Component Weight	1.333 g
Miscellaneous	Above 105C DC And AC Voltage Derating Is 4%/C.

Specifications

Capacitance	0.47 uF
Capacitance Tolerance	20%
Voltage AC	275 VAC
Voltage DC	630 VDC
Temperature Range	-40/+110°C
Rated Temperature	105°C
Dissipation Factor	0.1% 25C
Insulation Resistance	63.8298 GOhms
Max dV/dt	250 V/us
Resistance	118.5 mOhms (100kHz)
Ripple Current	1.2 Amps (100kHz 85C), 117.5 Amps (Peak)
Inductance	10 nH