### **AC Axial Fan**

# multicomp PRO



RoHS **Compliant** 

### **Specification**

Rated Voltage : 200V AC to 240V AC 50Hz/60Hz

Rated Current : 0.242 AMP @ 50Hz 0.255 AMP @ 60Hz

: 3.6 W@ 50Hz

Rated Power

3.9 W @ 60Hz

Tolerance : ±15% on Rated Power and Current

Rated Speed : 3100 RPM ±20% in Free Air at Rated Voltage @ 50Hz

3200 RPM ±20% in Free Air at Rated Voltage @ 60Hz

Max. Airflow At Zero Static Pressure : Nominal 40 / MIN. 34 CFM @ 50Hz

Nominal 41 / MIN. 34.9 CFM @ 60Hz

Max. Static Pressure At Zero Airflow : Nominal 0.14 / MIN. 0.12 inch-H<sub>2</sub>O @ 50Hz

> Nominal 0.15 / MIN. 0.13 inch-H<sub>2</sub>O @ 60Hz : Nominal 32 dB(A) / MAX. 36.8 dB(A) @ 50Hz

Acoustic Noise

Nominal 33 dB(A) / MAX. 37.9 dB(A) @ 60Hz

**Insulation Class** : UL CLASS : A

Ingress Protection : None

: 60,000 Hours at 40°C, 65% Humidity, 90% CL. Life Expectancy

Direction of Rotation : Counter-Clockwise From Blade Side

Electromagnetic Interference : X1 Capacitor 1.5uF/300V Min. (Optional, Across Line and Neutral of AC Power Input

Mechanical

Bearing System : Vapo Bearing System

: Thermoplastic PBT of UL 94V-0 Materials of Frame Materials of Fan Blade : Thermoplastic PBT of UL 94V-0 Impeller Balance Grade : G6.3 Per ISO 1940-1:2003(E)

Weight : 99.3 Grams

**Environmental** 

Operating Temperature Range : -20°C to +70°C Storage Temperature Range : -40°C to +70°C Operating Humidity Range : 5 to 90% RH Storage Humidity Range : 5 to 95% RH

**Protection** 

Over Temperature Protection


Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro



## **AC Axial Fan**



#### **Air Flow & Static Pressure Curve**




**NOTE**: The airflow and static pressure are measured with specific fixture.

#### **Dimensions**

Screw Type (Pan Head)	Torque	Screw Spec.	
		Size	Standard
Machine Screw	3∼4 kgf-cm	M4	JISB1111-1974
Self-Tapping Screw	5~6 kgf-cm	Ф5	JISB1122 Type 2

### **AC Axial Fan**

## multicomp PRO



Note:

1. Lead Wire: ULS3266 #24AWG Gray

2. Frame Type: Flange

Dimensions: Millimetres

#### **Part Number Table**

Description	Part Number	
AC Axial Fan, 80mm × 80mm × 25mm, 200V-240V AC	MP-CF2082HVL-10000-999	

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Page <3>

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

