AC Axial Fan

multicomp PRO

RoHS Compliant



Characteristics

Motor Design Insulation Resistance Dielectric Strength Motor Protection Noise Level

Tolerance Air Performance

Specification

| Rated Voltage | : 100V AC to 240V AC 50Hz/60Hz |
|------------------------------------|--|
| Operating Voltage Range | : 90V AC to 265V AC Hz |
| Safety Certification Voltage Range | : 100V AC to 240V AC Hz |
| Starting Voltage | : 85V AC (25°C Power ON/OFF) |
| Rated Speed | : 3500 RPM ±10% |
| Air Delivery | : 109 CFM / Min. 96.6 CFM |
| Static Pressure | : 0.37 Inch-H2O 0.31 Inch-H2O |
| Rated Current | : 81 mA 56mA |
| Rated Power | : 5.1 Watts |
| Noise Level | : 44.9 dB(A) / Max. 47.9 dB(A) |
| Direction of Rotation | : Counter-clockwise viewed from front of fan blade |
| Operating Temperature | : -25°C to +70°C |
| Storage Temperature | : -40°C to +70°C |
| Bearing System | : Precision ball bearing system |
| Weight | : 317g |
| Safety | : UL/CUR/TUV/CE/ATEX Approvals |
| Protection | : Automatic Restart Capability |
| Ingress Protection | : IP68 |

: Single phase, 4-poles Brushless DC motor.

: Measured in a semi-anechoic chamber with background noise level below 15 dB(A). The fan is running in free air with the microphone at a distance of one meter from the

: Measured by a double chamber. The values are recorded when the fan speed has

: 10 MΩ minimum at 500V DC.

: ±20% on rated power and current.

stabilized at rated voltage.

: 1800V AC for one second.

: Impedance Protected.


fan intake.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro



multicomp PRO

Performance Curves



Material

| Frame | : Thermoplastic PBT of UL 94V-0 |
|-----------|---------------------------------|
| Impeller | : Thermoplastic PBT of UL 94V-0 |
| Lead Wire | : UL 3266 #24AWG, Gray |

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro




AC Axial Fan

multicomp PRO

Dimensions

| Screw Type (Pan Head) | Torque | Screw Spec. | |
|-----------------------|------------|-------------|-----------------|
| | | Size | Standard |
| Machine Screw | 3~4 kgf-cm | M4 | JISB1111-1974 |
| Self-Tapping Screw | 5~8 kgf-cm | Ø5 | JISB1122 Type 2 |



Best Mounting Direction: Any orientation.

Dimensions : Millimetres

Part Number Table

| Description | Part Number | |
|--|-----------------------|--|
| AC Axial Fan, 120mm × 38mm, 100V-230V AC, IP68 | MP-CF4113HBL-0000-AED | |

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for white any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farrell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

