AC Axial Fan

multicomp PRO

RoHS Compliant




Specification

| Rated Voltage | : 100V AC to 240V AC 50Hz/60Hz |
|--|---|
| Rated Current | : 0.08 A @ 100V AC 0.045 A @ 240V AC |
| Rated Power | : 3.6 W |
| Tolerance | : ±20% on Rated Power and Current |
| Rated Speed | : 3100 RPM ±10% in Free Air at Rated Voltage |
| Max. Airflow at Zero Static Pressure | : Nominal 90.1 / MIN. 77.9 CFM Nominal 153 / MIN. 132 m³/h |
| Max. Static Pressure at Zero Airflow | : Nominal 0.31 / MIN. 0.25 inch-H₂O Nominal 77 / MIN. 62 Pa |
| Acoustic Noise | : Nominal 40.2 dB(A) / MAX. 44 dB(A) |
| Insulation Class | : F |
| Ingress Protection | : IP21 |
| Life Expectancy | : 70,000 Hours at 40°C, 15-65% RH. |
| Direction of Rotation | : Counter-Clockwise From Blade Side |
| Mechanical Bearing System Materials of Frame Materials of Fan Blade Impeller Balance Grade Weight | : Ball Bearing System : Thermoplastic PBT of UL 94V-0 : Thermoplastic PPS of UL 94V-0 : G6.3 Per ISO 1940-1:2003(E) : 265 Grams |
| Environmental Operating Temperature Range Storage Temperature Range Operating Humidity Range Storage Humidity Range | : -25°C to +70°C : -40°C to +70°C : 5 to 90% RH : 5 to 95% RH |
| Protection Automatic Restart Soft Start Over Load Protection Locked Rotor Protection | |

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

multicomp PRO



Air Flow & Static Pressure Curve

NOTE: The airflow and static pressure are measured with specific fixture.


Dimensions

| | Torque | Screw Spec. | | |
|-----------------------|------------|-------------|----------------|--|
| Screw Type (Pan Head) | | Size | Standard | |
| Machine Screw | 3~4 kgf-cm | M4 | JIS B1111-1974 | |

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro



multicomp PRO



| ltem | Functions | Wire Type | Colour | |
|----------|-----------|----------------|--------|--|
| AC Cable | L | UL 3266 #24AWG | Cray | |
| AC Cable | N | UL 3266 #24AWG | Gray | |

Dimensions : Millimetres

Part Number Table

| Description | | Part Number |
|-------------------------------|-------------------|------------------------|
| AC Axial Fan, 120mm × 38mm, 1 | 00V-240V AC, IP21 | MP-CF4113MBT-10000-AA9 |

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

