

# PRODUCT DATASHEET SST CLAS P60 DIM 5.5 W/2700 K FIL CL E14

LED Retrofit CLASSIC P DIM | Dimmable LED lamps, classic bulb shape



#### Areas of application

- Perfect for decorative installations
- Domestic applications
- General illumination
- Outdoor use in suitable outdoor luminaires only

#### **Product benefits**

- Lamps with innovative LED "filament" technology
- Very low energy consumption
- Instant 100 % light, no warm-up time
- Can be easily fitted instead of ordinary light bulbs
- Design, dimensions, luminous flux comparable to an incandescent lamp

#### **Product features**

- LED lamps for line voltage
- Dimmable (with many common dimmers, see also www.ledvance.com/dim)
- Beam angle: up to 300°
- Lifetime: up to 15,000 h
- Lamp made of glass





PRODUCT DATASHEET – Good quality of light; color rendering index  $R_a$ :  $\geq$  80; constant chromaticity


### **TECHNICAL DATA**

### Electrical data

Nominal wattage	5.5 W
Construction wattage	5.50 W
Nominal voltage	220240 V
Claimed equiv. conventional lamp power	60 W
Nominal current	37 mA
Type of current	AC
Inrush current	0.252 A
Operating frequency	50/60 Hz
Mains frequency	50/60 Hz
Max. lamp no. on circuit break. 10 A (B)	1785
Max. lamp no. on circuit break. 16 A (B)	2857
Total harmonic distortion	86 %
Power factor $\lambda$	≥ 0.50

#### Photometrical data

Luminous flux	806 lm
Luminous efficacy	146 lm/W
Lumen main.fact.at end of nom.life time	0.93
Light color (designation)	Warm White
Color temperature	2700 K
Color rendering index Ra	80
Light color	827
Standard deviation of color matching	≤6 sdcm
Flickering metric (Pst LM)	≤1.0
Stroboscope effect metric (SVM)	≤0.4



# Light technical data

Beam angle	300 °
Warm-up time (60 %)	< 0.50 s
Starting time	< 0.5 s

# **Dimensions & Weight**

Overall length	77.00 mm
Diameter	45.00 mm
Maximum diameter	45 mm
Product weight	15.00 g

# Temperatures & operating conditions

Ambient temperature range	-20+40 °C
Maximum temperature at tc test point	70 °C

### Lifespan

Lifespan	15000 h <sup>1)</sup>
Number of switching cycles	100000
Lumen maintenance at end of service lifetime	0.93
Rated lamp survival factor at 6,000 h	≥ 0.90

<sup>1)</sup> L70/B50

# Additional product data

Base (standard designation)	E14
Mercury content	0.0 mg
Mercury-free	Yes
Design / version	Clear
Product remark	All technical parameters apply to the entire lamp / Due to the complex production process for light-emitting diodes, the typical values shown for the technical LED parameters are purely statistical values that do not necessarily match the actual technical parameters of each individual product, which can vary from the typical value

# **Capabilities**

Dimmable	Yes <sup>1)</sup>

<sup>1)</sup> Check dimmer compatibility at ledvance.com/compatibility

#### Certificates & Standards

Energy efficiency class	D <sup>1)</sup>
Energy consumption	6.00 kWh/1000h
Type of protection	IP20
Standards	CE / ERP / RoHS / REACH / UKCA
Photobiological safety group acc. to EN62778	RGO

<sup>1)</sup> Energy efficiency class (EEC) on a scale of A (highest efficiency) to G (lowest efficiency)

# **Country-specific categorizations**

Order refe	ence	LEDSCLP60D 5,5W
LOGISTICA	L DATA	
Temperati	re range at storage	-20+80 °C

# Energy labelling regulation data acc EU 2019/2015

Lighting technology used	LED
Non-directional or directional	NDLS
Mains or non-mains	MLS
Light source cap-type (or other electric interface)	E14
Connected light source (CLS)	No
Color-tuneable light source	No
Envelope	No
High luminance light source	No
Anti-glare shield	No
Correlated colour temperature type	SINGLE_VALUE
Standby power	not applicable
Networked standby power for CLS	not applicable
Claim of equivalent power	Yes
Length	77.00 mm
Height	45.00 mm
Width	45.00 mm
Chromaticity coordinate x	0.463
Chromaticity coordinate y	0.420
R9 Colour rendering index	>0
Beam angle correspondence	SPHERE_360
Survival factor	0.90
Displacement factor	≥0.5

LED light source replaces a fluorescent light source	No
EPREL ID	1403347,523224,1373514
Model number	AC32317,AC45154,AC24256

#### **DOWNLOAD DATA**

	Documents and certificates
PDF	Declarations Of Conformity CE
	Photometric and lighting design files



Spectral power distribution

#### **LOGISTICAL DATA**

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075447875	Folding box 1	46 mm x 49 mm x 130 mm	27.00 g	0.29 dm³
4058075447882	Shipping box 10	251 mm x 111 mm x 106 mm	340.00 g	2.95 dm³
4058075611337	Shipping box 6	159 mm x 111 mm x 106 mm	220.00 g	1.87 dm³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

#### **DISCLAIMER**

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.