

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300480126](#)
Status: **Active**
Overview: Brad Micro-Change (M12) Connectors
Description: Micro-Change (M12) Double-Ended Cordset, 4 Poles, Male (Straight) to Male (Straight), 26 AWG, Teal PVC Cable, 5.0m (16.40') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E200650

General

Product Family Industrial Cordsets
 Series [130048](#)
 Connector End A Micro-Change (M12)
 Connector End B Micro-Change (M12)
 IP Rating IP67
 Material - Contact Copper Alloy
 Overview [Brad Micro-Change \(M12\) Connectors](#)
 Performance Category 5e
 Product Name Micro-Change (M12)
 Protocol N/A
 Region America, Asia, Europe
 Taxonomy Circular Industrial Cordsets
 Type Double Ended
 UPC 78678803804

Physical

Cable Diameter 5.59mm (.220")
 Cable Length 5.0m (16.40')
 Color - Cable Jacket Teal
 Coupling Style Threaded
 Gender Male-Male
 Keyway D-coded
 LED Indicator No
 Material - Cable Jacket PVC
 Material - Connector Body TPU
 Material - Coupling Nut Nickel-plated Brass
 Material - Plating Mating Gold
 Net Weight 269.433/g
 Orientation Straight to Straight
 Poles 4
 Temperature Range - Operating -20° to +75°C
 Wire Size AWG 26
 Wire/Cable Type Shielded PVC

Electrical


Current - Maximum per Contact 1.5A
 Voltage - Maximum 300V AC (RMS)

Material Info

Engineering Number E11A06015M050

Reference - Drawing Numbers

Sales Drawing 1300488146-000, SD-120108-020-001



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Contained Per - ED/01/2017 (12 January 2017)
 2,4-Di-tert-butyl-6-(5-chlorobenzotriazol-2-yl)p

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[130048 Series](#)

This document was generated on 09/04/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION