

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **1200878713**
Status: **Active**
Overview: Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable
Description: Nano-Change (M8) Double-Ended Cordset with Knurled Hexnut, 4 Poles, Male (Straight) to Female (Straight), 24 AWG, Black TPU WSOR Cable, 5.0m (16.40') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Cordsets
Series	<u>120087</u>
Connector End A	Nano-Change (M8)
Connector End B	Nano-Change (M8)
IP Rating	IP67
Material - Contact	Brass
Overview	<u>Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable</u>
Product Name	Nano-Change (M8)
Region	Europe
Taxonomy	Circular Industrial Cordsets
Type	Double Ended
UPC	889056073998

Physical

Cable Diameter	4.80mm (.189")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Coupling Style	Knurled Hexnut, Threaded
Gender	Female-Male
Keyway	A-coded
LED Indicator	No
Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	555.000/g
Orientation	Straight to Straight
Poles	4
Temperature Range - Operating	-25° to +85°C
Wire Size AWG	24
Wire/Cable Type	UL 21215

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	60V AC / 75V DC

Material Info

Engineering Number	444030B41M050
--------------------	---------------

Reference - Drawing Numbers

Sales Drawing	1200878716-000
---------------	----------------



Series image - Reference only

EU ELV

Compliant with Exemption 3

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2022)4187-DC (10 June 2022)
Lead

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

ELV

Not Relevant

Compliant with Exemption 3

RoHS Phthalates

ZZCERT_CE -

Not Contained

CER_4000410036_00_000.pdf

Declaration of

Conformity

ZZCERT_UKCA

- Declaration of

Conformity

CER_4000410293_00_000.pdf

Search Parts in this Series

120087 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION