

**RoHS
Compliant**




Specifications

Rated impedance 1.0kHz/0.57Vrms	: 8Ω ±15%
Rated input power	: 40mW
Max. input power	: 100mW
Resonant frequency F ₀ (in free field)	: 180 ±20%(Hz) with input
Frequency response & deviation	: 0.57V/1cm 20,000-40,000Hz
Sound pressure level at 1kHz with IEC318 coupler, 1mW, 1cm	: 122 ±3dB
Total harmonic distortion	: 5% Max. at 1kHz,0.57V
Voice coil diameter	: Ø13.28 mm
Magnet (nd)	: Ø27 × 17 × 4.0mm Ferrite
Operating temperature	: -20°C to +60°C
Storage temperature	: -25°C to +60°C
Weight	: 4.5g
Hand soldering	: For maximum 3 seconds 350 ±10°C

Material



Frame - ABS	Plate - SPCC
Yoke - SPCC	Magnet - Ferrite
Diaphragm - PET	PCB - FR4
Voice coil - Cu	Non woven fabric - Black/White

Diagram




Dimensions : Millimetres

Frequency Response Curve



Frequency Response Curve



Part Number Table

Description	Part Number
Miniature Speaker, 8Ω, 0.4W	MCABS-264-RC

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.