

Motor-protective circuit-breaker, 0.1 - 0.16 A, Feed-side screw terminals/
output-side push-in terminals



Powering Business Worldwide™

Part no. PKZM0-0,16-SPI16
 Catalog No. 199177
 Alternate Catalog No. XTPRSP16P16BC1NL
 EL-Nummer (Norway) 4312286

Delivery program

| | | | | |
|-----------------------------|----------|----|--|---|
| Product range | | | | PKZM0 motor protective circuit-breakers up to 32 A |
| Basic function | | | | Motor protection |
| | | | | |
| Notes | | | | Also suitable for motors with efficiency class IE3. |
| Connection technique | | | | Feed-side screw terminals/output-side push-in terminals |
| Max. motor rating | | | | |
| AC-3 | | | | |
| 660 V 690 V | P | kW | | 0.06 |
| Rated uninterrupted current | I_u | A | | 0.16 |
| Setting range | | | | |
| Overload releases | I_r | A | | 0.1 - 0.16 |
| | | | | |
| short-circuit release | | | | |
| | | | | |
| max. | I_{rm} | A | | 2.5 |
| Phase-failure sensitivity | | | | IEC/EN 60947-4-1, VDE 0660 Part 102 |

Technical data

General

| | | | | |
|---|--|-----------------|--|--|
| Standards | | | | IEC/EN 60947, VDE 0660, UL, CSA |
| Climatic proofing | | | | Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30 |
| Ambient temperature | | | | |
| Storage | | °C | | - 40 - 80 |
| Open | | °C | | -25 - +55 |
| Enclosed | | °C | | - 25 - 40 |
| Mounting position | | | | |
| Direction of incoming supply | | | | as required |
| Degree of protection | | | | |
| Device | | | | IP20 |
| Terminations | | | | IP00 |
| Protection against direct contact when actuated from front (EN 50274) | | | | Finger and back-of-hand proof |
| Mechanical shock resistance half-sinusoidal shock 10 ms to IEC 60068-2-27 | | g | | 25 |
| Altitude | | m | | Max. 2000 |
| Terminal capacity main cable | | | | |
| Screw terminals | | | | |
| Solid | | mm ² | | 1 x (1 - 6) 2 x (1 - 6) |

| | | | |
|---|--|-----------------|------------------------------------|
| Flexible with ferrule to DIN 46228 | | mm ² | 1 x (1 - 6) 2 x (1 - 6) |
| Solid or stranded | | AWG | 18 - 10 |
| Stripping length | | mm | 10 |
| Push-in terminals | | | |
| Solid | | mm ² | 1 x (0,5 - 2,5) 2 x (0,5 - 2,5) |
| flexible | | mm ² | 1 x (0,5 - 2,5) 2 x (0,5 - 2,5) |
| flexible with ferrules | | mm ² | 1 x (0,5 - 1,5) 2 x (0,5 - 1,5) |
| flexible with ultrasonic welded busbar end | | mm ² | 1 x (0,5 - 2,5) 2 x (0,5 - 2,5) |
| flexible with uninsulated wire end ferrule | | mm ² | 1 x (0,5 - 2,5) 2 x (0,5 - 2,5) |
| Solid or stranded | | AWG | 20 - 14 |
| Stripping length | | mm | 10 |
| Standard screwdriver | | | 3.0 x 0.5 |
| Specified tightening torque for terminal screws | | | |
| Main cable | | Nm | 1.7 |

Main conducting paths

| | | | |
|---|-------------|-------------------|-------|
| Rated impulse withstand voltage | U_{imp} | V AC | 6000 |
| Overvoltage category/pollution degree | | | III/3 |
| Rated operational voltage | U_e | V AC | 690 |
| Rated uninterrupted current = rated operational current | $I_u = I_e$ | A | 0.16 |
| Rated frequency | f | Hz | 50/60 |
| Current heat loss (3 pole at operating temperature) | | W | 5.39 |
| Impedance per pole | | mΩ | 68000 |
| Lifespan, mechanical | Operations | x 10 ⁶ | 0.1 |
| Lifespan, electrical (AC-3 at 400 V) | | | |
| Lifespan, electrical | Operations | x 10 ⁶ | 0.1 |
| Max. operating frequency | | Ops/h | 40 |
| Motor switching capacity | | | |
| AC-3 (up to 690V) | | A | 0.16 |

Trip blocks

| | | | |
|---|--|---------|-------------------------------------|
| Temperature compensation | | | |
| to IEC/EN 60947, VDE 0660 | | °C | - 5 ... 40 |
| Operating range | | °C | - 25 ... 55 |
| Temperature compensation residual error for T > 40 °C | | | ≤ 0.25 %/K |
| Setting range of overload releases | | x I_u | 0.6 - 1 |
| short-circuit release | | | Basic device, fixed: 15.5 x I_u |
| Short-circuit release tolerance | | | ± 20% |
| Phase-failure sensitivity | | | IEC/EN 60947-4-1, VDE 0660 Part 102 |

Rating data for approved types

| | | | |
|--------------------------------------|--|------|---|
| Switching capacity | | | |
| Maximum motor rating | | | |
| Three-phase | | | |
| 200 V 208 V | | HP | Hinweis: Motorleistung in diesem Bereich nach Bemessungsstrom berechnen. Angegebene Werte nach NEC Table 430-150 |
| 230 V 240 V | | HP | Hinweis: Motorleistung in diesem Bereich nach Bemessungsstrom berechnen. Angegebene Werte nach NEC Table 430-150 |
| 460 V 480 V | | HP | Hinweis: Motorleistung in diesem Bereich nach Bemessungsstrom berechnen. Angegebene Werte nach NEC Table 430-150 |
| 575 V 600 V | | HP | Hinweis: Motorleistung in diesem Bereich nach Bemessungsstrom berechnen. Angegebene Werte nach NEC Table 430-150 |
| Single-phase | | | |
| 230 V 240 V | | HP | 5 |
| Short Circuit Current Rating, type E | | SCCR | |
| 240 V | | kA | 65 |

| | | |
|--|------|---------------|
| 480 Y / 277 V | kA | 65 |
| 600 Y / 347 V | kA | 50 |
| Accessories required | | BK25/3-PKZ0-E |
| Short Circuit Current Rating, group protection | SCCR | |
| 600 V High Fault | | |
| SCCR (fuse) | kA | 50 |
| max. Fuse | A | 600 |
| SCCR (CB) | kA | 50 |
| max. CB | A | 600 |

Design verification as per IEC/EN 61439

| | | |
|--|----|-----|
| Technical data for design verification | | |
| Operating ambient temperature min. | °C | -25 |
| Operating ambient temperature max. | °C | 55 |

Technical data ETIM 8.0


| | | |
|---|----|--|
| Low-voltage industrial components (EG000017) / Motor protection circuit-breaker (EC000074) | | |
| Electric engineering, automation, process control engineering / Low-voltage switch technology / Circuit breaker (LV < 1 kV) / Motor protection circuit-breaker (ecl@ss10.0.1-27-37-04-01 [AGZ529016]) | | |
| Overload release current setting | A | 0.16 - 0.16 |
| Adjustment range undelayed short-circuit release | A | 2.5 - 2.5 |
| With thermal protection | | No |
| Phase failure sensitive | | Yes |
| Switch off technique | | Thermomagnetic |
| Rated operating voltage | V | 690 - 690 |
| Rated permanent current Iu | A | 0.16 |
| Rated operation power at AC-3, 230 V | kW | 0 |
| Rated operation power at AC-3, 400 V | kW | 0 |
| Type of electrical connection of main circuit | | Spring clamp connection |
| Type of control element | | Turn button |
| Device construction | | Built-in device fixed built-in technique |
| With integrated auxiliary switch | | No |
| With integrated under voltage release | | No |
| Number of poles | | 3 |
| Rated short-circuit breaking capacity Icu at 400 V, AC | kA | 150 |
| Degree of protection (IP) | | IP20 |
| Height | mm | 93.5 |
| Width | mm | 45 |
| Depth | mm | 75.1 |

Approvals


| | | |
|--------------------------------------|--|--|
| Product Standards | | IEC/EN 60947-4-1; UL 60947-4-1; CSA - C22.2 No. 60947-4-1-14; CE marking |
| UL File No. | | E36332 |
| UL Category Control No. | | NLRV |
| CSA File No. | | 165628 |
| CSA Class No. | | 3211-05 |
| North America Certification | | UL listed, CSA certified |
| Specially designed for North America | | No |
| Suitable for | | Branch circuit: Manual type E if used with terminal, or suitable for group installations |

Dimensions

| | | |
|---|--|--|
| Motor-protective circuit-breaker with standard auxiliary contact PKZM0-...(+NHI-E-...-PKZ0) PKZM0-...-T(+NHI-E-...-PKZ0) PKM0-...(+NHI-E-...-PKZ0) | | |
|---|--|--|



Motor-protective circuit-breakers with lockable rotary handles
PKZM0-...+AK-PKZ0



Motor-protective circuit-breakers with early-make auxiliary contacts
PKZM0-...+VHI-...-PKZ0

Additional product information (links)

| | |
|--|---|
| Schaltvermögen | https://de.ecat.eaton.com/flip-cat/?edition=MOTCONT1_DE#page_3/44 |
| Motor starters and "Special Purpose Ratings" for the North American market | http://www.eaton.eu/ecm/groups/public/@pub/@europe/@electrical/documents/content/pct_3258146.pdf |
| Busbar Component Adapters for modern Industrial control panels | http://www.moeller.net/binary/ver_techpapers/ver960en.pdf |