



General Information

Series	PEG124
Dielectric	Aluminum Electrolytic
Style	Axial
Description	Long Life Axial Aluminum Electrolytic
RoHS	Yes
Lead	Wire Leads
AEC-Q200	No
Halogen Free	Yes
Component Weight	19.7 g
Miscellaneous	Life Calculation Based On Maximum Ripple Current, Please Contact KEMET For More Information.
Notes	L1 is KEMET's recommendation for minimum distance between symmetrical Lead bend. Available only for Customer specific part numbers. Lead bend dimensions must be specified and confirmed per article. Dimensions D And L Include Sleevings.
Shelf Life	156 Weeks

Specifications

Capacitance	47 uF
Capacitance Tolerance	-10/+30%
Voltage DC	450 VDC
Temperature Range	-40/+105°C
Rated Temperature	105°C
Life	22000 Hrs
Ripple Current	0.377 Amps (100Hz 105C), 2.4 Amps (5kHz 60C), 0.89 Amps (5kHz 105C)
Leakage Current	63 uA (5min 20°C)

Dimensions

D	20mm +/-0.5mm
L	46mm +/-1mm
L1	52mm MIN
LL	42mm +3/-2mm
F	0.8mm +/-0.03mm

Packaging Specifications

Sleevings	Yes
Packaging	Tray